

# TECHNICAL DATA SHEET

**NIKOLA black Mid ESD S2 No. 74310**


**Sz. 36 - 42**



## LABELLING ACCORDING TO STANDARD

Standard for safety footwear EN ISO 20345 S2	Basic requirement for S2: <b>A</b> Antistatic shoe - <b>E</b> Energy absorption in the heel - <b>FO</b> Fuel resistance - <b>WRU</b> Water penetration and water absorption resistant upper - Closed heel area
Additional requirements	<b>SRA</b> Slip resistance: Slip resistant on floors of ceramic tiles with a sodium lauryl sulfate (SLS) solution.

## FORM

Ladies' safety boot 	Form B - in size 38, the upper height must be at least 10.5 cm.
--	---

## FIT

Ladies' fit	The shoe last is ideally tailored to the ergonomics of female feet.
-------------	---

## AREAS OF APPLICATION


Areas of application	Indoors and outdoors Areas where exposure to moisture is expected (S2)  Areas where there is a risk of electrostatic discharge (ESDS/ESD)  Business shoe that also fulfils the safety requirements stipulated for health and safety in the workplace: Managers, engineers, architects, factory superintendents etc.
----------------------	--

## FEATURES

ESD equipment	Thanks to its excellent discharge capability, the shoe is suitable for work in ESD sensitive or electrostatically protected areas (EPA). The shoes comply to the standard 61340-5-1.
---------------	--



## FEATURES

Certification in accordance with DGUV rule 112-191	<ul style="list-style-type: none"> <li>• Certified for orthopaedic inserts</li> </ul> 
Padded tongue	<ul style="list-style-type: none"> <li>• Excellent wearing comfort: The tongue prevents pressure marks.</li> </ul>
Collar padding	<ul style="list-style-type: none"> <li>• Excellent wearing comfort: the ankle-wrapping, softly padded upper edge provides for stability and grip in the shoe.</li> </ul>
Combination of lacing and zipper	<ul style="list-style-type: none"> <li>• Allows the boots to be put on and taken off quickly</li> <li>• Boots can be laced individually</li> </ul>


## UPPER MATERIAL

Cowhide leather	<ul style="list-style-type: none"> <li>• Areas of application S1/S2/S3</li> <li>• Natural material</li> <li>• Wear-resistant</li> <li>• Breathable</li> <li>• Water penetration/absorption in accordance with EN ISO 20345 S2</li> </ul>
-----------------	--


## LINING

Leather lining	<ul style="list-style-type: none"> <li>• High tear resistance</li> <li>• Breathable</li> <li>• Natural material</li> </ul>
Heel pocket lining	<ul style="list-style-type: none"> <li>• The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort.</li> </ul>

## TOE PROTECTION CAP

<p>Steel toe cap</p> 	<ul style="list-style-type: none"> <li>• Protection against impacts of min. 200 joules and pressure loading of min. 15 kN</li> <li>• Permanent edge coverage for cushioning</li> <li>• Ergonomically shaped</li> <li>• Comfortable toe room</li> <li>• Good coverage of the little toe area</li> </ul>
--	--

## INLAY SOLE

<p>Full-length inlay sole BUSINESS Lady</p> 	<ul style="list-style-type: none"> <li>• ESD EQUIPMENT: Protection against electrostatic discharge (ESD). The full-length, exchangeable inlay sole is conductive and designed for the use in ESD safety footwear according to the standards DIN EN ISO 20345 and DIN EN 61340-5-1.</li> <li>• The inlay sole is individually adapted to the fitting of safety footwear for women.</li> <li>• The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes.</li> <li>• The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate.</li> <li>• The extreme softness of the PU foam absorbs shocks on impact and increases walking comfort.</li> <li>• Improvement of the shoe climate thanks to the PU foam's open cell structure. So the foot is always kept comfortably dry.</li> </ul>
---	--

## INSOLE

ESD soft-fleece insole

ESD equipment: Protection against electrostatic discharge (ESD), and without using additional means fulfilling a bridge function to the outsole.

- Approximately 50 % lighter than comparable soles made of natural materials
- Flexible and shape-retaining
- Good air permeability
- Excellent wear resistance
- High moisture absorption
- Quick drying (virtually overnight)

## OUTSOLE

BUSINESS LADY mono-density sole with profile



- Excellent slip resistance
- Antistatic

Outsole: PU (polyurethane)

- Colour: black
- Profile depth: 2.5 mm
- Abrasion-resistant
- Heat-resistant to approx. 130°C
- Flexible at cold temperatures to approx. -20°C
- Oil and fuel resistant
- With heel