

KERN KFP 60V30LM-2022e

KERN

Platform



Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	930×545×230 mm
Net weight approx.	10 kg
Gross weight approx.	14 kg

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Piktogramme

STANDARD



FACTORY



Category

Brand	KERN
Product category	Measuring Technology Components
Product group	Platforms

Measuring System

Readability [d]	2 g
Weighing capacity [Max]	60 kg
Minimum weight [Min]	400 g
Loadcell type	stainless steel IP67 silicone-coated

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	20 g

Construction

Dimensions weighing platform (W×D×H)	500×400×110 mm
Dimensions weighing surface (W×D)	500×400 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Material load cell(s)	Stainless steels
Cable length	2,5 m
Allowed cable length display device [Max]	3 m
Levelling feet adjustable	✓
Load cells - number	1

Functions

IP protection - load cell	IP67
---------------------------	------