

Make your mark with the wheels that generations of craftsmen have chosen before you – Scotch-Brite™.

- Uncompromising quality Lasts long
- Finishes strong Repeatable results





## Corners aren't meant to be cut. Just deburred, sanded and polished.

Scotch-Brite™ Deburr & Finish PRO Unitised Wheels are ideal for both OEM use and for maintenance operations. They are soft, to reduce defects, yet wear like iron, for fewer wheel changeouts. These hard-working, high-performance products quickly blast through dirt, corrosion and other contaminants without loading and without changing part geometry – helping you get the job done faster.

## Faster, more consistent performance compared to the leading competitive wheel!


- 30 to 50% faster burr removal
- Up to 3× longer wheel life in deburring applications
- Minimal dust and debris less dust equals less cleanup
- Improved operator "feel"
- Minimises overcutting results in fewer rejects

# DONE RIGHT. DONE ONCE.

## The science of 3M Precision-Shaped Grain\*

Traditional non-woven abrasive products are constructed from particles of irregular-shaped abrasive materials, such as aluminum oxide, bound to a nylon web.

In our new Scotch-Brite™ Deburr & Finish PRO Unitised Wheels, conventional abrasive particles have been replaced with our proprietary ceramic precision-shaped grain. The hardness of the ceramic material, combined with the self-sharpening grain, provides longer life and helps you get the job done faster – without sacrificing the smooth feel and control you expect from Scotch-Brite™ abrasives.



<sup>\*</sup>This technology is included in our 4C, 6C and 8C products.



## Comparing cost-of-ownership

These are typical real-world results that customers have obtained using Scotch-Brite<sup>™</sup> Deburr & Finish PRO wheels compared to traditional deburring wheels.

Contact your local 3M representative to see how new Scotch-Brite<sup>™</sup> Deburr & Finish PRO wheels can help you improve productivity!

	•	
	Traditional deburring wheel	NEW Scotch-Brite Deburr & Finish PRO
Parts per wheel		
Labour per piece	OO:50 seconds	seconds
Reject rate		<b>X</b>
Operator feel		
Customer productivity	\$\$	\$\$\$\$\$

## performance advantages for yourself!

Do you use flap brushes, cartridge rolls or other specialty abrasives in your process? You may be able to improve performance and productivity by switching to Scotch-Brite<sup>™</sup> Deburr & Finish PRO wheels!

### Potential advantages:

- ▶ Longer life
- Faster burr removal
- Smoother feel
- Less dusting and debris
- Better finish

## **ORDERING INFORMATION**

### Scotch-Brite™ Roloc™ TR Deburr & Finish PRO Unitised Wheel

SAPID	UK part number	Size (mm) (diameter×thickness×centre hole)	Max RPM	Density	Grade	Qty/case
7010329346	51960	75 × 6 x NH	15,100	2S	FIN	40
7010300983	51957	75 × 3 x NH	15,100	4C	MED+	40
7010295274	51956	75 × 6 x NH	15,100	4C	MED+	40
7100081368	708774	50 × 3 x NH	22,100	6C	MED+	60
7100081367	708776	50 × 6 x NH	22,100	6C	MED+	60
7100081366	708777	75 × 3 x NH	15,100	6C	MED+	40
7100081365	708778	75 × 6 x NH	15,100	6C	MED+	40
7100109130	51958	75 × 3 x NH	15,100	8C	CRS+	40
7100109110	51959	75 × 3 x NH	15,100	8C	CRS+	40

#### Scotch-Brite™ Deburr & Finish PRO Unitised Disc

SAPID	UK part number	Size (inches) (diameter×centre hole)	Max RPM	Density	Grade	Qty/case
7010412238	51962	115 × 22.225	12,100	2S	FIN	5
7100081369	713542	115 × 22.225	12,100	6C	MED+	5
7100109111	51961	115 × 22.225	12,100	8C	CRS+	5

### Scotch-Brite<sup>™</sup> Deburr & Finish PRO Unitised Wheel

SAP ID	UK part number	Size (mm) (diameter×thickness×centre hole)	Max RPM	Density	Grade	Qty/case
7100143465	51977	75 × 6 × 6.35	18,100	2S	FIN	40
7100143460	51979	152 × 13 × 25.4	7,500	28	FIN	4
7100143476	51978	152 × 25 × 25.4	7,500	2S	FIN	2
7010365693	51968	75 × 6 × 6.35	18,100	4C	MED+	40
7010310029	51967	75 × 13 × 6.35	18,100	4C	MED+	20
7100083512	709320	25 × 25 × 4.8	35,100	6C	MED+	50
7100053414	707589	50 × 6 × 6.35	22,100	6C	MED+	60
7100053418	695631	75 × 3 × 6.35	18,100	6C	MED+	40
7100053419	695630	75 × 6 × 6.35	18,100	6C	MED+	40
7100053421	707592	75 × 19 × 6.35	15,100	6C	MED+	20
7100053422	707590	75 × 25 × 6.35	15,100	6C	MED+	10
7100103509	721912	75 × 3 × 9.525	18,100	6C	MED+	40
7100105326	51972	75 × 3 × 6.35	18,100	8C	CRS+	40
7100105529	51969	75 × 6 × 6.35	18,100	8C	CRS+	10
7100105530	51971	75 × 13 × 6.35	18,100	8C	CRS+	20
7100110912	51976	75 × 13 × 9.525	15,100	8C	CRS+	20
7010329496	51973	75 × 19 × 6.35	15,100	8C	CRS+	20
7100105568	51970	75 × 25 × 6.35	15,100	8C	CRS+	10
l use: on backsta	and or bench motor					
7010310028	51966	152 × 3 × 12.7	7,500	6C	MED+	16
7100088615	713835	152 × 3 × 25.4	7,500	6C	MED+	16
7100088614	715207	152 × 6 × 25.4	7,500	6C	MED+	8
7100088613	715208	152 × 13 × 12.7	7,500	6C	MED+	4
7010310025	51965	152 × 13 × 25.4	7,500	6C	MED+	4
7100088655	715209	152 × 25 × 12.7	7,500	6C	MED+	2
7100066553	51964	152 × 25 × 25.4	7,500	6C	MED+	2
7100110911	51975	152 × 13 × 25.4	7,500	8C	CRS+	4
7100111228	51974	152 × 25 × 25.4	7,500	8C	CRS+	2
7100108778	722917	203 × 13 × 12.7	5,500	8C	CRS+	4

### Available in 4 densities:

2S FIN: for polishing and finishing
4C MED+: for finishing and blending
6C MED+: for blending and deburring

• 8C CRS+: for heavy deburring or light weld removal



Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

#### **Abrasive Systems Division**

3M United Kingdom PLC Customer Service 4th Floor Building 8 Exchange Quay, Salford Quays Manchester M5 3EJ United Kingdom Tel: 0845 504 8772 abrasives.uk@mmm.com www.3M.co.uk/abrasives

3M Ireland Limited The Iveagh Building The Park, Carrickmines Dublin 18, Ireland Tel: 1800 320 500

Please recycle. Printed in the UK. © 3M 2018. 3M, Roloc and Scotch-Brite are trademarks of 3M Company. All rights reserved. J440171

