

## ALPINE 6683 S3

**WELDING BOOT EN ISO 20349:2010 SRC P FE AI HI-3 WRU FO HRO**

**SIZES: 38 - 48/49 (225 - 315) | FITTING OPTIONS: NB, XB (XXB)**



**S3** PROTECTION CLASS S3  
according EN ISO 20345

**4** ORIGINAL STEITZ MULTI-WIDTH SYSTEM  
4 different widths per shoe size

**SECURA VARIO® SYSTEM**  
weight dependent heel shock  
absorption

**ST** STEEL TOE CAP  
Toe cap made of steel

**STEEL MIDSOLE**  
puncture resistant steel midsole

**LEATHER-INSOLE**

**DGUV 191** INSOLE TREATMENT  
tested according to  
DGUV Rule 112-191

### FEATURES

- + Full-grained, easy-care smooth leather
- + Quick and easy 2-fold buckle fastener
- + Fire resistant NOMEX® yarn
- + Dust guard tongue
- + Ankle protection
- + Soft vamp-lining made of real leather
- + Full-length, removable comfort insole ERGO-SOFT with cushioning system and excellent moisture transportation

### OUTSOLE

#### Perbunan Alpine, anthracite

- + Outsole with a profile of 6,5 mm
- + Best possible scuff resistance and anti-slip properties
- + Hard-wearing and excellent cut resistance
- + Broad contact surface
- + Durable against acid and oil-based substances
- + Heat-resistant up to approx. 220° C



### CUSHIONING

#### SECURA VARIO® System

The replaceable, weight and pressure dependent heel shock absorption system ensures cushioning adapted to the individual needs of the wearer. The pressure load in the shoe is reduced to a natural extent and provides targeted relief to the back. At the same time, it helps to significantly reduce fatigue and increases the ability to compensate pressure loads by the leg and trunk musculature.

-  above 105 kg
-  up to 105 kg
-  up to 91 kg
-  up to 79 kg
-  up to 57 kg



The AGR quality cachet (Aktion Gesunder Rücken = Campaign for Healthier Backs): Certified and recommended by Association Forum Healthy Back – Better Living and Federal Association of German Back Schools.

More information:

AGR e.V., Stader Str. 6, D - 27432 Bremervörde,  
Phone +49 4761/92 63 580, [www.agr-ev.de](http://www.agr-ev.de)

