

VD PRO 1100 VF

SAFETY SHOE EN ISO 20345:2011 S1P SRC

SIZES: 36 - 50 (225 - 322) | FITTING OPTIONS: NB, XB (S, XXB)



S1P PROTECTION CLASS S1P according EN ISO 20345, additional puncture resistance

4 ORIGINAL STEITZ MULTI-WIDTH SYSTEM 4 different widths per shoe size

VF VARIO FLEX highly flexible, metal free puncture resistance with SECURA VARIO® SYSTEM

AL ALUMINIUM TOE CAP Toe cap made of aluminium

ESD Protection against electrostatic discharge

DGUV 191 INSOLE TREATMENT tested according to DGUV Rule 112-191

FEATURES

- + Ultra-lightweight microfibre combined with perforated design for optimal ventilation
- + Toe guard
- + Functional lining made of breathable textile and microfibre
- + Full-length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

OUTSOLE

- TPU Athletic ESD**, light-blue
- + Outsole with a profile of 3,5 mm
- + With increased protection against twisted ankles, reduced lever arms
- + Supports the natural movement
- + Light and flexible
- + Very good scuff resistance and anti-slip properties
- + Heat-resistant up to approx. 120 °C



CUSHIONING

VARIO Multiflex® Technology

Lever arms of the shoe force the foot to make unnatural movements and can lead to foot and Achilles tendon complaints, knee pain and back problems. Furthermore, lever arm forces can increase the risk of injuries such as sprained ankles. Lever arm reduced shoes are characterized by lower heel heights, increased insertion depth, softer material and lesser thickness of the sole, which is rounded in the peripheral areas. A result of the VARIO Multiflex® technology is the multiflexible outsole.

- above 105 kg
- up to 105 kg
- up to 91 kg
- up to 79 kg
- up to 57 kg



The AGR quality cachet (Aktion Gesunder Rücken = Campaign for Healthier Backs): Certified and recommended by Association Forum Healthy Back – Better Living and Federal Association of German Back Schools.

More information:
AGR e.V., Stader Str. 6, D - 27432 Bremervörde,
Phone +49 4761/92 63 580, www.agr-ev.de

