

# TECHNICAL DATA SHEET

MASTER F2A No. 89201


Sz. 36 - 48



## LABELLING ACCORDING TO STANDARD

<p>Standard for firefighting boots DIN EN 15090</p>	<p><b>Type 2:</b> all kinds of firefighting and rescue activities, where penetration protection and toe protection is needed.</p> <p><b>Subcategory F2A:</b> Basic shoe for type 2 + antistatic</p>
<p>Additional requirements</p>	<p><b>SRC Slip resistance:</b> Slip resistant on floors of ceramic tiles with a sodium lauryl sulfate (SLS) solution and on steel floors with glycerol. When it comes to slip resistance as defined by EN ISO 20345, SRC signifies the best possible rating a safety shoe can reach.</p> <p><b>HI<sub>3</sub> HEAT INSULATED</b> To max. 250 °C for 40 minutes</p> <p><b>HRO HEAT RESISTANT OUTSOLE</b> Heat resistance against contact heat, also during short-term high temperatures</p>


## FORM

<p>Fire-fighting pull-on boot</p> 	<p>Form D - in size 42, the upper height must be at least 28.0 cm.</p>
---	--

## AREAS OF APPLICATION

<p>Areas of application</p>	<p>Outdoor areas Suitable for areas with particularly high safety requirements, preferably for fire service operations Areas with severe effects of heat</p>
-----------------------------	--

## FEATURES

Certification in accordance with DGUV rule 112-191	<ul style="list-style-type: none"> <li>• Certified for orthopaedic inserts</li> </ul> 
Ankle padding	Excellent wearing comfort: the ankle-wrapping padding provides for stability and firm grip and prevents pressure marks.
Donning loops	<ul style="list-style-type: none"> <li>• Quicker into the boot: Loops make it easier to put the boots on.</li> </ul>
High boot without laces or zippers	<ul style="list-style-type: none"> <li>• Quick getting in and out</li> </ul>
Heel strap	<ul style="list-style-type: none"> <li>• Allows the boots to be put on quickly</li> </ul>
Seams made of heat-resistant Nomex® thread	<ul style="list-style-type: none"> <li>• Best possible protection against flames, heat and chemicals. Cleaning does not affect the heat resistance.</li> </ul>


## UPPER MATERIAL

Cowhide leather - fire-resistant	<ul style="list-style-type: none"> <li>• Areas of application S2/S3</li> <li>• Natural material</li> <li>• Wear-resistant</li> <li>• Breathable</li> <li>• Water penetration/absorption in accordance with EN ISO 20345 S2</li> </ul>
----------------------------------	---


## LINING

Breathable fabric lining	<ul style="list-style-type: none"> <li>• Climate-regulating</li> <li>• Good ventilation</li> <li>• Skin-friendly</li> <li>• High absorption and emission of moisture</li> </ul>
--------------------------	---

## TOE PROTECTION CAP

<p>Steel toe cap</p> 	<ul style="list-style-type: none"> <li>• Protection against impacts of min. 200 joules and pressure loading of min. 15 kN</li> <li>• Permanent edge coverage for cushioning</li> <li>• Ergonomically shaped</li> <li>• Comfortable toe room</li> <li>• Good coverage of the little toe area</li> </ul>
--	--

## INLAY SOLE

<p>Full-length inlay sole</p> 	<ul style="list-style-type: none"> <li>• The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes.</li> <li>• The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate.</li> <li>• Antistatic</li> </ul>
---	---

## INSOLE

Antistatic soft-fleece insole

Antistatic, even if 100 % dry, without using additional means fulfilling a bridge function to the outsole.

- Approximately 50 % lighter than comparable soles made of natural materials
- Flexible and shape-retaining
- Good air permeability
- Excellent wear resistance
- High moisture absorption
- Quick drying (virtually overnight)

## PENETRATION RESISTANCE

Steel midsole

Best possible protection from below: The corrosion-resistant midsole made of stainless steel complies with the penetration safety standard EN 12568 and furthermore fulfils the additional requirements for penetration protection in accordance with EN ISO 20344 / 20345. Particularly recommendable when working in areas where there is an increased risk of injuries due to pointed or sharp objects, such as in the construction industry.

## OUTSOLE

STEINAU mono-density tread sole with profile



- Excellent slip resistance
- Antistatic

Outsole: Rubber

- Colour: black
- Profile depth: 6.0 mm
- Particularly abrasion-resistant
- Heat-resistant to approx. 200°C, for short periods to 300°C
- Flexible at cold temperatures to approx. -20°C
- Oil and fuel resistant
- Resistant to a large number of chemicals (acids and alkalis)
- Notch-resistant