


KERN KFP 150V20M

KERN

Platform



Dimensions packaging (W×D×H)	555×930×220 mm
Net weight approx.	10 kg
Gross weight approx.	17 kg

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Piktogramme

STANDARD



FACTORY



Category

Brand	KERN
Product category	Measuring Technology Components
Product group	Weighing bridges

Measuring System

Readability [d]	5 g
Weighing capacity [Max]	60 kg; 150 kg
Minimum weight [Min]	400 g; 1 kg

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	20 g; 50 g

Construction

Dimensions weighing platform (W×D×H)	500×400×130 mm
Dimensions weighing surface (W×D)	500×400 mm
Material weighing plate	stainless steel
Material platform	steel, varnished
Material load cell(s)	aluminium
Cable length	2,5 m
Allowed cable length display device [Max]	3 m
Levelling feet adjustable	✓
Load cells - number	1

Functions

IP protection - load cell	IP65
---------------------------	------

Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service