

# KERN KFP 150V30M

# KERN

Platform



## Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	930×555×220 mm
Net weight approx.	10 kg
Gross weight approx.	14 kg

## Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

## Piktogramme

### STANDARD



### FACTORY



## Category

Brand	KERN
Product category	Measuring Technology Components
Product group	Platforms

## Measuring System

Readability [d]	5 g
Weighing capacity [Max]	150 kg
Minimum weight [Min]	1 kg
Loadcell type	stainless steel IP68 encapsulated

## Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	50 g

## Construction

Dimensions weighing platform (W×D×H)	500×400×137 mm
Dimensions weighing surface (W×D)	500×400 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Material load cell(s)	Stainless steels
Cable length	2,5 m
Allowed cable length display device [Max]	3 m
Levelling feet adjustable	✓
Load cells - number	1

## Functions

IP protection - load cell	IP67
---------------------------	------