

## CP 4100 BOA SF

**SAFETY SHOE EN ISO 20345:2011 S1P SRC**

**SIZES: 36 - 50 (225 - 322) | FITTING OPTIONS: NB, XB (S, XXB)**



**S1P** **PROTECTION CLASS S1P**  
according EN ISO 20345,  
additional puncture resistance

**C** **COMPOSITE TOE CAP**  
Metal free toe cap, made of  
composite materials

**ESD**  
Protection against electrostatic  
discharge

**BOA** **BOA® FIT SYSTEM**  
for a fast, effortless, precision fit.

**4** **ORIGINAL STEITZ MULTI-WIDTH SYSTEM**  
4 different widths per shoe size

**SF** **TEXTILE PUNCTURE RESISTANCE**  
highly flexible, metal free  
puncture resistance

**DGUV 191** **INSOLE TREATMENT**  
tested according to  
DGUV Rule 112-191

### FEATURES

- + Ultra-light microfibre and large-scale inserts of netting with high ventilation quality
- + BOA® Fit System
- + Reinforced, abrasion-resistant TPU-toe guard

- + Functional lining made of breathable textile and microfibre
- + Full-length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

### OUTSOLE

#### TPU Competition ESD, white

- + Outsole with a profile of 3 mm
- + With increased protection against twisted ankles, reduced lever arms
- + Light and flexible
- + Cushioning structure in the heel area
- + Best possible scuff resistance and anti-slip properties
- + Heat-resistant up to approx. 120 °C



### CUSHIONING

#### REBOUND Technology

In the heel area, proven standard PU material stabilizes and absorbs the energy at the heel touchdown. In the midfoot and forefoot area, the midsole material with rebound effect returns a very high part of the energy spent by the wearer. In addition, the outsole made of soft TPU optimizes the power transmission in the step sequence.

