

## CP 4340 SF

**SAFETY SHOE EN ISO 20345:2011 S3 SRC**

**SIZES: 36 - 50 (225 - 322) | FITTING OPTIONS: NB, XB (S, XXB)**



**S3** PROTECTION CLASS S3  
according EN ISO 20345

**C** COMPOSITE TOE CAP  
Metal free toe cap, made of composite materials

**SF** TEXTILE PUNCTURE RESISTANCE  
highly flexible, metal free puncture resistance

**DGUV 191** INSOLE TREATMENT  
tested according to DGUV Rule 112-191

**4** ORIGINAL STEITZ MULTI-WIDTH SYSTEM  
4 different widths per shoe size

**METAL FREE**

**ESD**  
Protection against electrostatic discharge

### FEATURES

- + Ultra-light smooth microfibre with striking high frequency embossing
- + Comfortable fit due to seamless shoe design
- + Reinforced, abrasion-resistant TPU-toe guard
- + Metal-free design with protection against perforation
- + Functional lining made of breathable textile and microfibre
- + Full-length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

### OUTSOLE

#### TPU Competition ESD, white

- + Outsole with a profile of 3 mm
- + With increased protection against twisted ankles, reduced lever arms
- + Light and flexible
- + Cushioning structure in the heel area
- + Best possible scuff resistance and anti-slip properties
- + Heat-resistant up to approx. 120 °C



### CUSHIONING

#### REBOUND Technology

In the heel area, proven standard PU material stabilizes and absorbs the energy at the heel touchdown. In the midfoot and forefoot area, the midsole material with rebound effect returns a very high part of the energy spent by the wearer. In addition, the outsole made of soft TPU optimizes the power transmission in the step sequence.

