

NORA SF

WOMEN SAFETY SHOE EN ISO 20345:2011 S3 SRC  
SIZES: 35 - 42 (217 - 270) | FITTING OPTIONS: NB, XB (S, XXB)



- S3

**PROTECTION CLASS S3**  
according EN ISO 20345
- AL

**ALUMINIUM TOE CAP**  
Toe cap made of aluminium
- ESD

**ESD**  
Protection against electrostatic discharge
- 4

**ORIGINAL STEITZ MULTI-WIDTH SYSTEM**  
4 different widths per shoe size
- SF

**TEXTILE PUNCTURE RESISTANCE**  
highly flexible, metal free  
puncture resistance
- DGUV 191

**INSOLE TREATMENT**  
tested according to  
DGUV Rule 112-191


FEATURES

- + Ultra-light smooth microfibre with striking high frequency embossing
- + Comfortable fit due to seamless shoe design
- + Reinforced, abrasion-resistant TPU-toe guard
- + TPU heel trim for stabilization
- + Dust flap
- + Functional lining made of breathable textile and microfibre
- + Full-Length, removable comfort insole ERGO-SOFT ESD with cushioning system and excellent moisture transportation

OUTSOLE

**TPU Woman Sport ESD, silvergrey**

- + Outsole with a profile of 3 mm
- + Light and flexible
- + With tailored arch support
- + Best possible scuff resistance and anti-slip properties
- + Heat-resistant up to approx. 120 °C



CUSHIONING

**Multiflex® Technology**

Lever arms of the shoe force the foot to make unnatural movements and can lead to foot and Achilles tendon complaints, knee pain and back problems. Furthermore, lever arm forces can increase the risk of injuries such as sprained ankles. Lever arm reduced shoes are characterized by lower heel heights, increased insertion depth, softer material and lesser thickness of the sole, which is rounded in the peripheral areas. A result of the Multiflex® technology is the multiflexible outsole.

