

TECHNICAL DATA SHEET

jo_FLEX blue Low ESD S1P No. 12481


Sz. 40 - 48



LABELLING ACCORDING TO STANDARD

| | |
|--|---|
| Standard for safety footwear EN ISO 20345 S1P | Basic requirement for S1P: A Antistatic shoe - E Energy absorption in the heel - FO Fuel resistance - P Penetration resistance - Closed heel area |
| Additional requirements | SRC Slip resistance: Slip resistant on floors of ceramic tiles with a sodium lauryl sulfate (SLS) solution and on steel floors with glycerol. When it comes to slip resistance as defined by EN ISO 20345, SRC signifies the best possible rating a safety shoe can reach. |



FORM

| | |
|--|--|
| Safety shoe  | Form A - in size 42, the upper height must not exceed 11.2 cm. |
|--|--|

AREAS OF APPLICATION

| | |
|----------------------|---|
| Areas of application | Dry work areas Industry, storage, transport, assembly etc. Areas where there is a risk of penetration from pointed and sharp objects (S1P) Areas where there is a risk of electrostatic discharge (ESDS/ESD) |
|----------------------|---|

FEATURES

| | |
|--|--|
| ESD equipment | Thanks to its excellent discharge capability, the shoe is suitable for work in ESD sensitive or electrostatically protected areas (EPA). The shoes comply to the standard 61340-5-1.  |
| Certification in accordance with DGUV rule 112-191 | <ul style="list-style-type: none"> • Certified for orthopaedic inserts  |
| Padded upper edge | <ul style="list-style-type: none"> • Excellent wearing comfort: the padded upper edge protects the Achilles tendon. |

FEATURES

| | |
|----------------------------------|--|
| Padded tongue | <ul style="list-style-type: none"> • Excellent wearing comfort: The tongue prevents pressure marks. |
| Seamless upper material | The upper material comes without disturbing / damageable threads: This is why the shoe can easily adapt to the natural shape of the foot. Painful pressure marks are prevented thanks to the seamless workmanship. |
| Leather-free equipment | <ul style="list-style-type: none"> • Suitable for persons allergic to leather |
| PU toe protection (polyurethane) | <ul style="list-style-type: none"> • Directly applied tip protection • Excellent wear protection in the shoe tip area • Protects the upper material in this area against premature wear |


UPPER MATERIAL

| | |
|------------------|--|
| Textile material | <ul style="list-style-type: none"> • Areas of application S1 • Synthetic material • Retains its shape • Tear-resistant • Quick drying • Abrasion resistant and light |
|------------------|--|


LINING

| | |
|--------------------------|---|
| Breathable fabric lining | <ul style="list-style-type: none"> • Climate-regulating • Good ventilation • Skin-friendly • High absorption and emission of moisture |
| Heel pocket lining | <ul style="list-style-type: none"> • The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort. |

TOE PROTECTION CAP

| | |
|--|--|
| <p>Steel toe cap</p>  | <ul style="list-style-type: none"> • Protection against impacts of min. 200 joules and pressure loading of min. 15 kN • Permanent edge coverage for cushioning • Ergonomically shaped • Comfortable toe room • Good coverage of the little toe area |
|--|--|

INLAY SOLE

| | |
|--|--|
| <p>Full-length inlay sole JORI ESD</p>  | <ul style="list-style-type: none"> • ESD EQUIPMENT: Protection against electrostatic discharge (ESD). The full-length, exchangeable inlay sole is conductive and designed for the use in ESD safety footwear according to the standards DIN EN ISO 20345 and DIN EN 61340-5-1. • The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes. • The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate. |
|--|--|

PENETRATION RESISTANCE

Metal-free penetration protection

The textile midsole complies with the penetration safety standard EN 12568 and furthermore fulfils the additional requirements for penetration protection in accordance with EN ISO 20344 / 20345. The light and flexible material enables an increased elasticity of the shoe, which can particularly be recognized when working on uneven grounds or on your knees.

The textile variant offers 100 % foot coverage compared to steel midsoles (foot coverage 85 % due to limits in the shoe manufacturing process). Being 100 % metal-free and antimagnetic, this equipment is used as penetration protection in safety shoes.

OUTSOLE

jo_TIGHT double-density sole with profile



- Excellent slip resistance
- Antistatic

Outsole: PU (polyurethane)

- Colour: lightgrey
- Profile depth: 4.2 mm
- Particularly abrasion-resistant
- Heat-resistant to approx. 130°C
- Flexible at cold temperatures to approx. -20°C
- Oil and fuel resistant

Midsole: PU (polyurethane)

- The soft PU core provides a good impact absorption and high wearing comfort