


**Transport equipment**

# Product data sheet

Article no.: 6838 Lifting table cart



Sectional steel/steel plate construction, powder coated anthracite RAL 7016. Sturdy tubular push handle. Hydraulic pump with chromium-plated piston. Operation via pedal control. Lowering valve precisely adjustable via hand lever. 2 castor and 2 fixed wheels, wheels with Polyurethane tyres, castor wheels with lock. Tubular push handle fixed with screws.

## Technical Details:

<b>Total load capacity (kg)</b>	1000
<b>Lifting range (mm)</b>	520 - 2000
<b>Length of usable platform (mm)</b>	1200
<b>Width of usable platform (mm)</b>	800
<b>Total length (mm)</b>	1430
<b>Total width (mm)</b>	800
<b>Tyres</b>	Polyurethane
<b>Wheel size (mm)</b>	200 x 50
<b>Note</b>	Stroke per pedal kick: 12 mm
<b>Weight (kg)</b>	242
<b>Country of origin</b>	China
<b>Warranty (years)</b>	2
<b>Customs tariff number</b>	84279000
<b>GTIN</b>	4017976368382