Scotch[™] "Silver Splice" Splittable Flying Splice Tape with Built-in Sensor-Repulpable 9990N for Newsprint

Product Data Sheet

Apr. 2011 Supersedes: Feb. 2010

Product Description

A double coated, splittable tape construction designed for straight line flying splices, furnished with 2 repulpable acrylic adhesives and an easy release paper liner (also repulpable), with liner score for easy manual application and a built-in sensor layer (eliminating need for the traditional Aluminium sensor label on the splice pattern).

Key Features

The built-in Aluminium sensor within tape construction eliminates the need for the traditional reflective label needed for splice detection. The very soft splicing side adhesive is designed for good "instant grab" on uncoated newsprint.

Physical Properties

Adhasiya Typa	Plus Populpoble on	
Adhesive Type	Blue Repulpable on	
Splicing side	Aluminium laminate	
Adhesive Type	Clear Repulpable	
reel side		
Tape Color	Blue (splicing side)	
	White (tabbing side)	
	White splittable non-	
Carrier	siliconised tissue /	
	aluminium foil laminate	
Thickness		After splitting
(ASTM D-3652)	Before splitting	Splice side
Tape	0.135 mm	0.080 mm
Liner	0.060 mm	Reel side
Total	0,195 mm	0,055 mm
	cleavable layer,	
	recessed 2 mm in	
Splittable Layer	from leading tape	
-	edge	
	Silicone coated semi-	
Release Liner	bleached Kraft paper	

Performance Characteristics

Repulpability *	Adhesive and	
	Liner Completely *	
Bonding Strength	Excellent affinity	
	to Cellulose	
	Fibres	
	Lower Paper Wt	Upper Paper Wt
Paper weight / speed**	Test Limits	Test Limits
	37,5 mm:	37,5 mm:
	40 g, 600 m/min	60 g, 530 m/min
	50 mm: 40 g, 590 m/min	50 mm: 60 g, 530 m/min

Applications

Designed for: <u>Flying splice</u> of paper webs in the printing industry in cold set processes where no heat is used during the printing process

Flying splice of paper webs in newsprint.

*Repulpability

Repulpability is tested according to TAPPI UM 213, Procedure A. It is important to follow the weight and quantity measurement for fibre, splicing tape and water. Non-representative results can occur if test guidelines are not followed. The adhesives, carrier and liner are repulpable according to this test method, however, the presence of the aluminium sensor in the construction renders the <u>tape</u> non-repulpable according to TAPPI UM 213, Procedure A.

** Paper weight / Speed

Lower and upper limits of paper weight and splicing speed represent the limits of successful testing of this and other related constructions carried out during field trials on core and belt driven presses or on other appropriate paper manufacturing equipment. The paper weight and splicing speed limits given do not imply that this product will not perform well on papers outside these limits. They are only an indication that testing has not been completed outside these limits. We recommend consultation with 3M technical service for processes involving paper weights and splicing speeds outside the abovementioned limits. Please note that thorough testing is necessary to ensure suitability of this product to the user's individual splicing conditions and requirements.

Storage

3M Scotch™ Silver Splice Splittable Flying Splice Tape with Built-in Sensor Repulpable 9990N for Newsprint should be stored in the original carton at 21°C (70°F) & 50 % Relative Humidityor refrigerated in the original carton for maximum shelf life. If the product is refrigerated, it should be allowed to warm to a temperature of at least 21°C before using. It is recommended that the protective liner be removed just prior to splicing, rather than leaving paper rolls with prepared splice patterns in storage without the protective liner.

Shelf Life

3M Scotch™ Silver Splice Splittable Flying Splice Tape with Built-in Sensor Repulpable 9990N for Newsprint has a shelf life of 12 months from date of manufacture by 3M when stored in the original carton at 21°C (70°F) & 50 % Relative Humidity.

Precautionary Information	Refer to product label and Material Safety Data Sheet for health and safety information before using the product. For information please contact your local 3M Office. www.3M.com	
For Additional Information	To request additional product information or to arrange for sales assistance, please call your local sales representative. Address correspondence to: 3M	
Important Notice	All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.	

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications.

This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark of the 3M Company.

3M United Kingdom PLC

2M Centre, Cain Road, Bracknell RG12 8HT United Kingdom

3M Ireland Ltd

The Iveagh Building, 3rd Floor The Park, Carrickmines 18 Ireland

3M Belgium bvba/sprl

Hermeslaan 7 1831 Diegem Belgium

3M Nederland B.V.Molengraaffsingel 29
2629 JD Delft
The Netherlands

3M Svenska AB Herrjärva torg 4

170 67 Solna Sweden

3M a/s

Hannemanns Allé 53 DK-2300 Copenhagen S. Denmark

3M Norge AS

Tærudgata 16 2004 Lillestrøm Norway

Suomen 3M Oy Keilaranta 6 02150 Espoo Finland 3M Eesti OÜ

Pärnu mnt. 158 11317 Tallinn Estonia

3M Latvia SIA

K.Ulmaņa gatve 5 Rīga, LV-1004 Latvia

3M Lietuva UAB

A.Goštauto g. 40 Vilnius LT- 03163 Lithuania