# 3M Dual Lock™ Reclosable Fastener SJ3870

# **Product Data Sheet**

January 2017 Supersedes: New

#### **Product Description**

3M™ Dual Lock™ Reclosable Fastener SJ3870 contains a modified acrylic adhesive. The fastener consists of continuous strips of polyolefine with 250 polyolefine stems per square inch having a mushroom shaped top.

#### **Key Features**

- Modified acrylic adhesive bonds to medium to high surface energy substrates (e.g. metal, ABS)
- Stem density: 250 stems/in<sup>2</sup>
- Closure cycle life > 1 000
- Mushroom shaped stems snap in place to ensure fastener is engaged
- · Good aging performance and resistance against humidity
- Good initial adhesion
- · Quick and easy to install
- Durable for indoor and outdoor applications

# **Physical Properties**

Туре	SJ3870
Adhesive Type	Modified acrylic adhesive
Tape Colour	Black
Backing	Black polypropylene
Stems	Black polypropylene
Release Liner	3M branded filmic liner
Engaged Thickness acc. DIN EN 1942: 2008	5.8 mm

### **Performance Characteristics**

Туре	SJ3870
90 ° Peel adhesion to Stainless Steel acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	42 N/cm
90 ° Peel adhesion to PP acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	3 N/cm
90 ° Peel adhesion to ABS acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	53 N/cm
90 ° Peel adhesion to Stainless Steel acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell and after 10d @ 38 °C & 98 % rH	33 N/cm
Dyn. Tensile Engagement Strength acc. to ASTM D897-08, tested @ RT	113 N/in²
Dyn. Tensile Disengagement Strength acc. to ASTM D897-08, tested @ RT	231 N/in²
Dyn. Tensile Disengagement Strength acc. to ASTM D897-08, tested @ 70 °C	72 kPa
Dynamic Shear – Max. Force acc.ISO 29863:2007 to aluminium	83 kPa
Dynamic Shear – Elongation acc.ISO 29863:2007 to aluminium	69 %
Static Shear Strength Stainless Steel ISO 29863:2007, after 72h @ RT dwell (Holds minimum 77.5 g/cm² for 10.000 minutes)	23 ° C – 500 g 70 ° C – 500 g
"T" Peel (flexible to flexible) acc. ISO 29862:2007	50 N/cm

# Storage & Shelf Life

Store at 16 °C - 25 °C and 40 - 65 % relative humidity in its original box. The product can be stored up to 24 months after production.

**Note:** The shelf life may be shortened if the original packaging is not properly sealed or stored in an environment with high temperatures or humidity.

#### For Additional Information

To request additional product information or to arrange for sales assistance, call.....

Address correspondence to: 3M

#### **Important Notice**

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark of the 3M Company.

#### 3M Afrique Francophone

Société à responsabilité limitée Au capital de 19.756.400 Dirhams Siège Social: ZF Ksar Almajaz Bureau 6 Plateforme Lot n°2 Immeuble 4 zénith Tanger R.C: 74327, I.F.: 18745050

#### 3M Arabia, LLC

Building 24-25 3M Saudi Arabia Zone C, Business Gate Airport Road Riyadh Saudi Arabia

#### 3M Egypt

Finance Center, New Cairo Plot 140, Banking Sector 5th settlement Cairo Egypt

#### 3M Gulf Limited

Dubai Internet City Building No. 11, 3rd Floor U.A.E

### **3M Gulf Limited**

Ein El Mreisseh Saint Charles City Center, 4th Floor P.O.Box: 11-5025 Riad el Solh Beirut 1107 2180 Lebanon

#### 3M Gulf (Representation Office)

Suhaim Bin Hamad St. Al Mana Towers Tower B, 2nd Floor, Office No.4 Doha Qatar P.O.Box 14684

# 3M Kenya Ltd

Victoria Towers, 3rd Floor Kilimanjaro Av, Upperhill Kenya

#### 3M Maroc

Société à responsabilité limitée Au capital de 18.000.000 de Dirhams Siège Social: 33, lot la colline II Sidi Maarouf -Casablanca R.C:78517, I.F.: 1084514 Morocco 3M Minnesota Mining and Manufacturing Nigeria Limited No 2 Sheraton Opebi Link Road

Ikeja Lagos Nigeria

#### 3M Pakistan

Islamic Chamber of Commerce Building ST-2/A, Block 9, KDA Scheme 5, Clifton, Karachi Pakistan

# 3M South Africa and Sub-Saharan Africa

146A Kelvin Drive Woodmead Sandton South Africa