

Trizact™ Film Disc 468LA

Product Data Sheet

Date 09/2020 Supersedes: NEW

| 3M I.D. Number | 468LA | |
|------------------------------|--|--|
| Product Description | 3M™ Trizact™ 468LA Film Disc uses microreplication technology with Silicon Carbide mineral coated on a film backing. This product is used in automotive paint defect repair. | |
| Mineral | Silicon Carbide | |
| Backing | 3 mil film backing | |
| Dimensions | Various sizes for discs on rolls are available with Stickit™ attachment method. | |
| Storage | Store at 16 °C – 26 °C and 35-50 % relative humidity in its original box on "first-in - first-out" cycle. Note: The shelf life may be shortened if the original packaging is not properly sealed or stored in an environment with high temperatures or humidity. | |
| Precautionary Information | Refer to Product Label and Safety Instruction Leaflet for health and safety information before using the product. For information please contact your local 3M Office. www.3M.com | |
| For Additional Information | To request additional product information or to arrange for sales assistance, call your local 3M Application Engineering. | |
| Important Notice | All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law | |

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

For Additional Information

| 3M UK Limited 3M Abrasive Systems Division 3M Centre Cain Road Bracknell RG12 8HT Tel: 08705 360036 abrasives.uk@mmm.com 3M.co.uk/metalworking | 3M Ireland Limited 3M Abrasive Systems Division The Iveagh Building The Park Carrickmines Dublin 18 Ireland Tel: 1800 320 500 | 3M Denmark a/s 3M Abrasive Systems Division Afd. Industri Hannemanns Allé 53 2300 København S Telefon 43 48 01 00 www.3M.dk |
|--|---|---|
| 3M Finland Suomen 3M oy 3M Abrasive Systems Division Keilaranta 6 PL 600 02151 Espoo Puh: 09 525 21 www.3M.fi | 3M Svenska AB Herrjarva torg 4 S170 67 Solna SWEDEN Telefon 08-92 21 00 E-post kundservice@mmm.com www.3M.se | 3M Norge AS 3M Abrasive Systems Division Avd. Industri Postboks 100 2026 Skjetten Tel: 0 63 84 www.3M.no |
| 3M Latvija 3M Abrasive Systems Division K. Ulmaņa gatve 5 Rīga, LV-1004 Telefons +371 67 066 120 www.3M.lv | 3M Eesti OÜ 3M Abrasive Systems Division Pärnu mnt 158 11317 Tallinn Eesti Telefon +372 611 5900 www.3M.ee | 3M Lietuva, 3M Abrasive Systems Division UAB A. Goštauto g. 40A LT-03163, Vilnius Lietuva Tel. +370 5 2160 119 www.3M.lt |

3M is a trademark of the 3M Company.