


Transport equipment

Product data sheet

Article no.: B1335P Chair truck



For transporting stacked chairs. Of tubular construction. A combination of stacking trolley B1325P with chair carrying facility. Sturdy welded construction, powder coated blue RAL 5007. Curved top bar and transversal struts. For safe transport of circular items such as rolls, cans, buckets etc. Safety grips, punctureproof PU-tyres on synthetic rims, hubs with roller bearings. The carrying arms are engaged to the trolley and can be adjusted to variable heights. When not in use as a chair trolley the arms will fold back to the main frame so that the trolley can be used for other purposes. Carrier arms: Length: 500 mm, width: 250 mm, capacity: 70 kg. (German patent: 10 2004 034 195)

Technical Details:



Total load capacity (kg)	300
Blade width (mm)	320
Blade depth (mm)	250
Total width (mm)	580
Total depth (mm)	884
Total height (mm)	1300
Tyres	Polyurethane material
Wheel size (mm)	260 x 85
Version	für Stühle
Note	Capacity carrying facility: 70 kg
Weight (kg)	16,7
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976131221