

1460 ESD Kraftform Micro torque screwdrivers with a customised factory pre-set measurement value with quick-release chuck, 1461 ESD x 0.05-0.11 Nm
7400 ESD series Kraftform Torque screwdrivers, with factory pre-set value of your choice



| | | | |
|------------------------|---|-------------------------------|--------------|
| EAN: | 4013288188311 | Size: | 128x18x18 mm |
| Part number: | 05074810010 | Weight: | 122 g |
| Article number: | 1460 ESD Micro customized pre-set, Halfmoon | Country of origin: | CZ |
| | | Customs tariff number: | 82054000 |

- Customized pre-set, adjustable Kraftform ESD torque screwdriver
- ESD-safe tool thanks to surface resistance of $\leq 10^9$ Ohm
- Distinct audible and perceivable excess load signal when the pre-set torque value is reached
- Suitable for the take-up of bits with 4 mm halfmoon drive and 4 mm HIOS drive
- Applications e.g. on smartphones, mobile phones, cameras, electronic equipment

With a customised factory pre-set torque value. The torque can be changed with an extra tool within the measuring range (re-calibration kit can be ordered with the code number 05137004001). Afterwards you can check the set value using an off-the-shelf torque tester. Compact handle/interchangeable blades system for torque-controlled precision screwdriving. The Kraftform Micro ESD torque screwdriver is ideal for torque-controlled jobs on electrostatically sensitive components. Suitable for bits with a 4 mm Halfmoon drive (Wera series 9) and a 4 mm HIOS drive (Wera series 21). Tamper-proof. Clearly audible and tactile signal when the set torque is reached. Repeatability is 100% guaranteed. Unlimited manual loosening torque. Electrical surface resistance $\leq 10^9$ ohms for safe protection against electrostatic charge. Manufactured as per DIN EN 61340-5-1. Handle/interchangeable blades system for rapid blade changes. Kraftform Micro handle with rotating cap and free-turning zone for rapid turning, making any time-consuming repositioning of the fingers unnecessary. Power zone with integrated soft zones ensures the transmission of high tightening and loosening torques. Precision zone directly above the blade for the correct rotation angle for adjustment work. Rapid bit fixing: Simply push the bit into the holder for automatic locking and a secure fit. To change the bit, simply push the sleeve forward and remove the bit. Free-running actuating sleeve for easy handling of the tool during the screwdriving process. Bits suitable for manual and machine operated screwdriving connections with electric screwdrivers (including HIOS, Delvo, Sehan). Use with e.g. smartphones, mobile phones, cameras, electronic devices, in dental laboratories and dental surgeries. Please note: 1 Ncm = 0.01 Nm.



Web link

https://products.wera.de/en/torque_tools_7400_esd_series_kraftform_torque_screwdrivers_with_factory_pre-set_value_of_your_choice_1460_esd_micro_customized_pre-set

Wera - 1460 ESD Micro customized pre-set, Halfmoon
05074810010 - 4013288188311

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

1460 ESD Krafftform Micro torque screwdrivers with a customised factory pre-set measurement value with quick-release chuck, 1461 ESD x 0.05-0.11 Nm
 7400 ESD series Krafftform Torque screwdrivers, with factory pre-set value of your choice



Customised pre-setting

Wera ESD Tools

High protection

For Halfmoon and HIOS Bits




Wera torque screwdriver. With a customised factory pre-set torque value. For all applications, where the same constant torque and repeat accuracy are required.



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.



The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.



Features a combination bitholder for both bits with Halfmoon and bits with HIOS drive.

The power zone

The precision zone


The fast-turning zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.



The fast-turning zone just below the rotating cap allows rapid twisting.

Web link

https://products.wera.de/en/torque_tools_7400_esd_series_krafftform_torque_screwdrivers_with_factory_pre-set_value_of_your_choice_1460_esd_micro_customized_pre-set



Wera - 1460 ESD Micro customized pre-set, Halfmoon
 05074810010 - 4013288188311

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

1460 ESD Kraftform Micro torque screwdrivers with a customised factory pre-set measurement value with quick-release chuck, 1461 ESD x 0.05-0.11 Nm
 7400 ESD series Kraftform Torque screwdrivers, with factory pre-set value of your choice



Further versions in this product family:

| | |  |  |  | |
|--|---------------------------------|---|---|---|---------------|
| | art. no. | Nm | mm | inch | |
| | 05074800010 ¹⁾ | 1460 ESD | 0.02-0.06 | 131 | 5 1/4" |
| | 05074810010¹⁾ | 1461 ESD | 0.05-0.11 | 131 | 5 1/4" |

1) The desired settings can be made in the following units: Nm, kgf. m, lbf. ft., ozf. in., dN. m, kgf. cm, lbf. in, in. oz, cN. m, gf. m, ft. lb, gf. cm, in. lb.

Web link

https://products.wera.de/en/torque_tools_7400_esd_series_kraftform_torque_screwdrivers_with_factory_pre-set_value_of_your_choice_1460_esd_micro_customized_pre-set

Wera - 1460 ESD Micro customized pre-set, Halfmoon
 05074810010 - 4013288188311

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de