



Data Sheet

REACH
1907/2007/EC

Heat Shrinkable Moulded Parts

3M™ SKE 4-Way Cable Breakouts



Description

3M Cable End Caps and 3-, 4-Way Breakouts are designed for quick and easy insulation and sealing of cable end or crutches, and provide resistance to abrasion, weathering and chemical attack. Each Heat Shrink part will cover a wide range of sizes and different kind of cables.

Electrical Markets Division
3M United Kingdom PLC
Sales Office
PO Box 393
Bedford MK41 0YE
Telephone: 0870 609 4639
Fax: 01234 229 433

3M Ireland Ltd
Sales Office
The Iveagh Building, The Park,
Carrickmines, Dublin 18, Ireland
Telephone: (01) 800 812 732
Fax: 353 1 280 3509

3M United Kingdom PLC
Head Office
3M Centre, Cain Road
Bracknell, Berkshire RG12 8HT
Telephone: 01344 858 000
Fax: 01344 858 758

Technical Information

These parts are made from semi-rigid, cross-linked modified polyolefin material, which is internally coated with hot melt adhesive. The materials used are halogen free.

On application of heat the adhesive melts and the part shrinks forming a perfect watertight seal. They can be used for insulating/sealing of cable crutches for indoor and outdoor applications.

Dimensions

Product Description	Application Range on LV cable	Ø Neck Exp.	Ø Neck Recov.	Ø Finger Exp.	Ø Finger Recov.	Length Recov.	Wall Thickness Neck Recov.	Wall Thickness Finger Recov.
	mm ²	mm	mm	mm	mm	mm	mm	mm
SKE 4F/0	-	28	09	08	02	80	2.0	1.5
SKE 4F/1+2	4 - 35	35	15	15	04	100	3.8	1.8
SKE 4F/3+4	25 - 150	57	23	30	06	170	4.0	3.0
SKE 4F/5	120 - 400	95	36	38	14	220	3.5	2.5
SKE 4F/6	-	117	36	46	14	220	3.5	2.5

Electrical Markets Division
3M United Kingdom PLC
Sales Office
 PO Box 393
 Bedford MK41 0YE
 Telephone: 0870 609 4639
 Fax: 01234 229 433

3M Ireland Ltd
Sales Office
 The Iveagh Building, The Park,
 Carrickmines, Dublin 18, Ireland
 Telephone: (01) 800 812 732
 Fax: 353 1 280 3509

3M United Kingdom PLC
Head Office
 3M Centre, Cain Road
 Bracknell, Berkshire RG12 8HT
 Telephone: 01344 858 000
 Fax: 01344 858 758

Material Characteristics

The figures are average values, established to our best knowledge, but not to be used for specification purpose.

Physical Properties	Value	Test Method
Density	1.05 ± 0.2 g/cm ³	ASTM D-1505/D=M/V
Hardness	45 ± 3 shore D	ASTM D-2240
Tensile strength	10 N/mm ²	ASTM D-412 / ISO 37
Ultimate elongation	300 %	ASTM D-412 / ISO 37
Water absorption	0.15 %	ASTM D-570 / ISO 62
Longitudinal Shrinkage	10 %	-
Recovery Temperature	120 °C	IEC - 216
Peel strength	100 N/25 mm	Rolling Drum method
Thermal Tests		
Operating temperature range	- 30 °C, + 135 °C	DIN 53 466
Thermal Ageing (150 °C for 168 hrs)		
Tensile strength	8 N/mm ²	ASTM D-412 / ISO 37
Ultimate elongation	200 %	ASTM D-412 / ISO 37
Flammability	Not self extinguishing	ASTM D 876
Low Temperature Flexibility	- 40 °C	ASTM D 2671C
Electrical Properties		
Volume resistivity	1 x 10 ¹³ Ohm-cm	ASTM D-257 / IEC 93
Dielectric strength	10 kV/mm	ASTM D-149 / IEC 243
Chemical Properties		
Corrosion	None	ASTM D 2671

Electrical Markets Division
3M United Kingdom PLC
Sales Office
 PO Box 393
 Bedford MK41 0YE
 Telephone: 0870 609 4639
 Fax: 01234 229 433

3M Ireland Ltd
Sales Office
 The Iveagh Building, The Park,
 Carrickmines, Dublin 18, Ireland
 Telephone: (01) 800 812 732
 Fax: 353 1 280 3509

3M United Kingdom PLC
Head Office
 3M Centre, Cain Road
 Bracknell, Berkshire RG12 8HT
 Telephone: 01344 858 000
 Fax: 01344 858 758