

TECHNICAL DATA SHEET

SECUMAX 320 MDP

NO. 32000771

Safety technology



Concealed blade – a maximum degree of safety

The SECUMAX 320 MDP blade is not an open one, but is hidden from people and goods. This provides you with a maximum degree of safety from cut injuries and from damage to goods.



SAFETY KNIFE WITH CONCEALED BLADE, ESPECIALLY FOR CUTTING FILM AND PLASTIC STRAPPING BAND.

Order No. 32000771.02

COMBI reloaded. The new generation. Metal detectable.

The SECUMAX COMBI MDP was always in a class of its own as a film cutting expert – until it found its legitimate successor. The new SECUMAX 320 MDP makes an instant impression with its outstanding design. And if you look more closely, you will appreciate its inner values. For example, in comparison to its predecessor, the perfected ergonomics and the completely overhauled blade change. What about the subject of "metal detectability"? It has always been in the COMBI MDP's DNA – and so it will remain that way.

Metal-detectable plastic

The SECUMAX 320 MDP is metal detectable and especially suited to companies and sectors processing sensitive materials. Even the tiniest fragment of the knife can be traced before any contamination of your products takes place.

Safety first

The concealed blade and rounded nose reliably protects you and your products. Furthermore, the knife head has been

significantly strengthened making it more robust and longer lasting.

Blade change made easy


Another handling and safety benefit is the newly designed blade change. Simply lift up at the blade change button and remove the cover. You can then directly access the 4-cutting edge blade.


Perfect ergonomics


Can you feel the difference? The new handle shape with the finger friendly contours fits like a glove. The preset cutting angle is also kind to the hand and arm helping you to position the knife for cutting.

Optimised blade section

Just two examples: The cutting channel is formed so that your safety knife moves away the freshly cut material even faster. Diagonal cuts are also easier than ever to perform. Your benefits: Less effort required for the task.







PRODUCT FEATURES

Technical features



Maximum safety



Metal detectable



X-ray detectable



Safer blade change (with magnet)



Abrasion resistant



Very ergonomic



4-cutting edge blade



Cutting depth



Tape splitter



For right and left handers



Lanyard hole



Stainless

Main cutting materials



Wrapping, stretch, and shrink foil



Layers of foil or paper



Plastic strapping band



Cardboard: 1-ply



Tape



Bagged goods



Textile, material



Felt



Safety belt



Leather



Coated film



Laminated film


Installed blade




NO. 192043

0,40 mm, deep-edged, stainless

BLADE CHANGE



Fully open the blade carrier from the handle using the blade change button.



Place the thumb on the blade symbol and open up the blade cover. Remove the blade from the **side**. Turn or change the blade.



Then align the blade to the left edge and insert exactly onto the locating lugs.



Close the blade cover and fold the blade carrier back into the handle letting the blade change button audibly snap into place.



Safety poster



Training video



Technical data sheet



Consulting service

PRODUCT AND PACKAGING DETAILS

Order No.	NO. 32000771.02	Packaging unit	1 in single unit box
Knife size (L x W x H)	158 x 13 x 56 mm	Size Single unit box	168 x 19 x 62 mm
Weight knife	60.0 g	Weight single unit box	71.0 g
Basic material	Metal detectable plastic	EAN Code single unit box	4002632800917
Cutting depth	4 mm	Quantity in outer pack	10 knives
		Size outer pack	128 x 98 x 173 mm
		Weight outer pack	825.0 g
		EAN Code outer pack	4002632850912
		Customs tariff number	82119200

SAFETY CERTIFICATE

Date of issue	04.07.2018	
Certification	GS certificate NR. 603646-6680-55094-2018/1	

Certificates and awards



SECURITY ADVICE

To ensure that you use your new MARTOR knife safely and most effectively, please read and note the following user-instructions. Please keep the written guide in a safe place so that you can access it at any time.

- **1. General application instructions:** Please always use the product carefully for manual cutting work only and not for any purposes other than those that are intended. Please take the correct handling and the proper use of the knives into account in this regard. As an additional safety measure, we recommend the wearing of safe gloves.
- 2. Special application instructions to avoid the danger of injuries: Only use knives that are in perfect condition and have sharp, clean and undamaged MARTOR blades. Employ the utmost care when handling the knives. Prior to use, familiarise yourself with the safety features and their functioning. Ensure that these safety features are not impaired by the type of material to be cut. CAUTION: The blade is sharp and can result in serious and deep cuts. Therefore, never reach into the blade! Do not place your free hand in the line of cutting and never cut directly towards you.
- **3. Replacement of spare parts:** Replace any blades that become dull at the right time! Use only the replacement blades from MARTOR for this purpose. Dispose of old blades in a

proper fashion. They should not be placed in a waste paper bin, as this poses a considerable danger of injuries. Never perform any repairs yourself. If the knife shows signs of aging or any other wear, e.g. which impair safety features, blade changing or usage, the knife must be taken out of service and replaced. Do not modify this product in any way. Modifications of any kind may impair product safety. CAUTION: The risk of injury caused by manipulation of this product is extremely high.

- **4. Non-use of the knife:** Always secure the blade in such a way (depending on product type) that injuries due to cuts are excluded. Store the knife in a secure place.
- **5. Care instructions:** To guarantee a long service life, always keep the knife clean and do not expose it to unnecessary soiling and humidity.

CAUTION: No liability will be assumed for consequential losses. Subject to technical changes and errors! This knife does not belong in the hands of children!

BELT HOLSTER M WITH CLIP NO. 9921



USED BLADE CONTAINER NO. 9810



WALL MOUNT BRACKET USED BLADE CONTAINER



Include it in your order now! With this mounting bracket you can fix your USED BLADE CONTAINER to a central location. Use the clamp and screws and nuts supplied with the product to attach it to either a pipe or a rod.

What do you do with your cutting tools when you are not ac-

tually using them? The MARTOR BELT HOLSTER M is a robust

holder that allows you to carry all midsize MARTOR knives as well as our safety scissors at all times. In addition, the interior and exterior pockets are designed to allow you to load different tools: for example you can carry an extra safety knife, a pen and a pack of blades. The MARTOR BELT HOLSTER is the ideal place to stow your tools safely when moving from A to B - and have them at hand, as soon as they are required.

You can fill the USED BLADE CONTAINER with the content of

your SAFEBOX. Or directly with your used blades. When the

box is full, turn the lid until it shuts. Now the box cannot be reopened. The next step is to safely and completely dispose of the filled USED BLADE CONTAINER as normal waste.

SAFEBOX NO. 108000

NO. 9845



The SAFEBOX is large enough to store a large number of used blades safely. And at the same time, it is compact enough to carry with you. The two slits are not only used for filling, but also to "shorten" your snap-off blades. When your SAFEBOX is full, empty it into your USED BLADE CONTAINER.

MDP TEST CARD SET NO. 9910



There are five cards with different plastic balls in the MDP TEST CARD SET – between 2.5 mm and 8 mm in size. You can reliably test the effectiveness of your metal detectors using the "visiting card".

MANUFACTURER

MARTOR KG | Lindgesfeld 28 | 42653 Solingen | Germany T +49 212 73870-0 | info@martor.de | www.martor.com