3M Scotch™ Splittable Flying Splice Tape Repulpable 9356

Product Data Sheet

September 2015 Supersedes: April 2012

Product Description

A double coated, splittable tape construction designed for straight line flying splices, furnished with repulpable acrylic adhesive on both sides and an easy release paper liner (also repulpable), with liner score for easy manual application.

Key Features

- Good shear and heat resist for higher speed splicing on core driven printing presses, or on an off-machine coater- with improved adhesion to a wide range of papers
- A colour stabilized blue dye has been added to the splicing side adhesive to render the prepared splice pattern more visible after removing the liner just prior to splicing.
- Modified splittable layer to provide a slightly higher overall splitting force for improved splice reliability in higher speed processes.

Physical Properties

Adhesive Type Splicing side	Blue Repulpable	
Adhesive Type Reel side	Clear Repulpable	
Tape Colour	Blue (splicing side)	
	White (tabbing side)	
Carrier	White splittable non-siliconised tissue	
Thickness (ASTM D-3652)	Before splitting	After splitting
Tape without liner	0.138 mm	Splice side 0.084 mm
Liner	0.060 mm	Reel side 0.055 mm
Total	0.198 mm	
Splittable Layer	Cleavable layer, recessed 2 mm in from	
	leading tape edge	
Release Liner		
	Silicone coated semi-bleached Kraft paper	

Repulpability *	Tape and Liner Completely *	
Bonding Strength	Good affinity to Cellulose Fibres	
* is tested according to TAPPI UM 213, Procedure A. It is important to follow the		

weight and quantity measurement for fibre, splicing tape and water. Nonrepresentative results can occur if test guidelines are not followed.

The adhesives, carriers and liner are repulpable according to this test method.

Applications	Designed for: Flying splice of paper webs in the paper industry
	Flying splice of paper webs on an Off-Machine Coater or on core driven printing presses. Not intended for use on belt driven printing presses.
Storage	3M™ Scotch™ Splittable Flying Splice Tape Repulpable 9356 should be stored in the original carton at 18°C - 25°C and 45 - 55 % Relative Humidity or refrigerated in the original carton for maximum shelf life. If the product is refrigerated, it should be allowed to warm to a temperature of at least 21°C before using. It is recommended that the protective liner be removed just prior to splicing, rather than leaving paper rolls with prepared splice patterns in storage without the protective liner.
Shelf Life	12 months from date of manufacture by 3M when stored in the original carton.
Precautionary Information	Refer to product label and Material Safety Data Sheet for health and safety information before using the product. For information please contact your local 3M Office. www.3M.com
For Additional Information	To request additional product information or to arrange for sales assistance, please call your local sales representative. Address correspondence to: 3M
Important Notice	All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications.

applicable, to the prevailing law.

This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

3M United Kingdom PLC

2M Centre, Cain Road, Bracknell RG12 8HT United Kingdom

3M Ireland Ltd

The Iveagh Building, 3rd Floor The Park, Carrickmines 18 Ireland

3M Belgium bvba/sprl

Hermeslaan 7 1831 Diegem Belgium

3M Nederland B.V.

Molengraaffsingel 29 2629 JD Delft The Netherlands

3M Svenska AB

Herrjärva torg 4 170 67 Solna Sweden

3M a/s

Hannemanns Allé 53 DK-2300 Copenhagen S. Denmark

3M Norge AS

Tærudgata 16 2004 Lillestrøm Norway

Suomen 3M Oy

Keilaranta 6 02150 Espoo Finland

3M Eesti OÜ

Pärnu mnt. 158 11317 Tallinn Estonia

3M Latvia SIA

K.Ulmaņa gatve 5 Rīga, LV-1004 Latvia

3M Lietuva UAB

A.Goštauto g. 40 Vilnius LT- 03163 Lithuania