

Product Datasheet model uvex ultravision 9301 064



**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

1. Product Characteristics


- classic goggles with unrestricted field of vision
 - can be worn over prescription spectacles
 - lenses can be changed
 - high mechanical strength of the polycarbonate lens (B: 120 m/s)
 - highly wearing comfort thanks to indirect ventilation
 - with CBR65-lens technology
- Contrast** (contrast-enhancing)
Blue (reduction of blue light)
Relax (relaxed view)
65 (65% transmission)

2. Technical Details Body

Frame

Material	PVC
Version	indirect ventilation
Colour	transparent grey

Headband	
Material	synthetic
Features	individually adjustable
Colour	black, grey
Marking	
Manufacturer 's ID code	W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles)
Impact resistance	B (120 m/s)
Resistance to high speed particles at extremes of temperature	T
Conformity symbol	CE

3. Technical Details Lens	
Material	PC
Thickness	2,2 mm at PD
Coating	uvex supravision excellence
Colour	light brown (CBR65)
UV protection	UV400
Marking	
Filter	5-1,4 (EN 172)
Manufacturer 's ID code	W
Optical class	1
Impact resistance	B (120 m/s)
Resistance to high speed particles at extremes of temperature	T
Scratch resistance	K
Antifog	N
Conformity symbol	CE
Factory symbol	

4. Miscellaneous

Weight	131g
Packing	90 goggles per carton
Standards	EN 166 + EN 172
PPE Category	Category II