

## Product Datasheet uvex 2 6523.1-4 S3 HI HRO SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth**

<b>Product information</b>	<ul style="list-style-type: none"><li>• Sporty, multifunctional safety shoes</li><li>• Extremely light and flexible</li><li>• The latest generation of 100% metal-free uvex xenova® toe cap. Compact design, anatomical shape, good side and ankle twist stability, no thermal conductivity and antimagnetic properties</li><li>• Metal-free, penetration-resistance insole in accordance with the latest standard, which does not impact shoe flexibility</li><li>• Made with new high-performance technology for exceptional wearer comfort</li><li>• uvex climazone technology for optimum comfort</li><li>• Water-repellent, breathable and extremely soft leather upper</li><li>• Distance mesh lining provides optimum breathability</li><li>• Virtually seam-free construction to eliminate pressure points</li><li>• Removable comfort insole, antistatic, with moisture control system and additional shock absorption in the heel and at the front of the foot</li><li>• Soft, padded collar and padded tongue</li><li>• Injection-moulded polyurethane scuffcap to protect upper leather on toe cap and significantly extend resistance time</li><li>• Meets ESD requirements: resistance to ground &lt; 35 megaohm</li></ul>
<b>Outsole</b>	<ul style="list-style-type: none"><li>• Lightweight two-layer insole with excellent shock absorption characteristics and outstanding slip resistance</li></ul>

	<ul style="list-style-type: none"> <li>• Multilayer shock absorption system comprising PU mid sole, highly slip resistance rubber outsole from Vibram and comfortable insole, shock absorption in the front and heel: all this protects the musculoskeletal system, even over long periods of time</li> <li>• Optimised ankle protection to ensure safety when working on ladders</li> <li>• Rugged, self-cleaning sole ridges ensures maximum grip for demanding applications on uneven or dirty floors (SRC labelling).</li> <li>• withstands brief exposure to heat of approx. +300°C</li> </ul>																				
<b>Technical Data</b>	<table> <tr> <td>Art.-no.</td> <td>6523.1</td> <td>.2</td> <td>.3</td> <td>.4</td> </tr> <tr> <td>Fitting</td> <td>10</td> <td>11</td> <td>12</td> <td>14</td> </tr> <tr> <td>Standard</td> <td colspan="4">EN ISO 20345:2011 S3 HI HRO SRC</td> </tr> <tr> <td>Size</td> <td colspan="4">35 – 52</td> </tr> </table>	Art.-no.	6523.1	.2	.3	.4	Fitting	10	11	12	14	Standard	EN ISO 20345:2011 S3 HI HRO SRC				Size	35 – 52			
Art.-no.	6523.1	.2	.3	.4																	
Fitting	10	11	12	14																	
Standard	EN ISO 20345:2011 S3 HI HRO SRC																				
Size	35 – 52																				
<b>Accessories</b>	<p><i>uvex 1 comfortable climatic insole</i> (article no.: 9534.7-9 + .0)</p> <ul style="list-style-type: none"> <li>• Provides the foot with exceptional, full-surface shock absorption and ensures comfort in high-strain zones</li> <li>• Ultra breathable and moisture-absorbing materials</li> <li>• Shock absorption zones that assist natural movement</li> <li>• Non-irritating, comfortable surface structure</li> </ul> <p><i>Laces</i></p> <ul style="list-style-type: none"> <li>• Black (article no.: 9599.9 11)</li> </ul>																				