

Product Datasheet uvex 2 xenova 9556.1 - .3 S3 SRC

**UVEX ARBEITSSCHUTZ GmbH, Würzburger Str. 181-189, D-90766 Fürth**

General features	<ul style="list-style-type: none">• Ultra low weight and versatile S3-safety boot• upper: water-repellent, full-grain smooth leather• PU-coated leather scuffcap to protect upper leather on toe cap and significantly extend resistance time• All sole materials are free of silicones, plasticisers and other paint wetting impairment substances• Heat-resistant lace loop system
Protection features	<ul style="list-style-type: none">• Meets ESD requirements: resistance to ground < 35 megaohm• 100% metal-free uvex xenova® toe cap. Compact design, anatomical shape, good lateral stability, no thermal conductivity properties• Penetration-resistant, non-metallic midsole in accordance with the latest safety standards, does not restrict flexibility of the shoe• Ergonomically designed outsole made from dual density polyurethane with excellent slip resistance
Comfort features	<ul style="list-style-type: none">• Light weight and optimised shock absorption• Outstanding wearer comfort results from a newly developed last and climate-optimised, breathable materials• Removable comfort insole, antistatic, with moisture control system and additional shock absorption in the heel and at the front of the foot• Soft padding on collar and dust tongue
Outsole	<ul style="list-style-type: none">• PUR outsole, non-marking• Ergonomically designed tread• Extremely flexible, excellent shock absorption• Unique PUR outsole system makes the shoe ultra-light

	<ul style="list-style-type: none"> • Two-layer system with abrasion-resistant and cut-resistant outsole • Excellent slip resistance • Self-cleaning tread • Resistant to oil and petrol • Resistant to temperatures for short periods up to ca. +120°C 																
Certificates	<ul style="list-style-type: none"> • Certified with uvex medicare for individual, orthopaedic inlay soles and individual adjustments of the sole unit such as overall increase, inside and outside increase and other solutions. 																
Areas of application	<ul style="list-style-type: none"> • Moderate applications 																
Technical data	<table> <tr> <td>Art.-no.</td> <td>9556.1</td> <td>.2</td> <td>.3</td> </tr> <tr> <td>Width</td> <td>10</td> <td>11</td> <td>12</td> </tr> <tr> <td>Standard</td> <td colspan="3">EN ISO 20345:2011 S3 SRC</td> </tr> <tr> <td>Size</td> <td colspan="3">38 – 52</td> </tr> </table>	Art.-no.	9556.1	.2	.3	Width	10	11	12	Standard	EN ISO 20345:2011 S3 SRC			Size	38 – 52		
Art.-no.	9556.1	.2	.3														
Width	10	11	12														
Standard	EN ISO 20345:2011 S3 SRC																
Size	38 – 52																
Accessories	<p><i>comfortable climatic insole</i> (Article-no.: 9534.7-9)</p> <ul style="list-style-type: none"> • Provides the foot with exceptional, full-surface shock absorption and ensures comfort in high-strain zones • Ultra breathable and moisture-absorbing materials • Shock absorption zones that assist natural movement • Non-irritating, comfortable surface structure <p><i>Shoe laces</i></p> <ul style="list-style-type: none"> • black (Article-no.: 9599.9 11) 																