

## Product data sheet for uvex rubiflex NB40S



For these chemical protection gloves, a thicker cotton interlock lining is used. This makes the uvex rubiflex S suitable for many applications in which protection against chemicals and increased mechanical protection (for example against heat) is required. The special 60 or 80 cm version is also available with elasticated gauntlet end.

### Characteristics

- Ergonomic fit
- Good grip
- Very good tactile feel

<b>Material number</b>	98902
<b>Sizes</b>	8 - 11
<b>Standard</b>	EN 420:2003 + A1:2009, EN 388:2016, EN ISO 374-1:2016
<b>Test chemicals</b>	n-Heptane (J), Sodium hydroxide 40% (K), Acetic acid 99% (N), Ammonia water 25% (O), Hydrogen peroxide 30% (P), Formaldehyde 37% (T)
<b>Performance class in accordance with EN 388</b>	2 1 2 1 X
<b>Performance class in accordance with EN 407</b>	X 1 X X X X
<b>Outer material</b>	Cotton interlock
<b>Coating</b>	Nitrile rubber (NBR)
<b>Coating surface area</b>	Fully coated
<b>Coating thickness</b>	0.50 mm
<b>Type</b>	With gauntlet
<b>Colour</b>	Green
<b>Glove length</b>	40 cm

EN ISO 374-1:2016 / Type A



JKN OPT

EN 388:2016



2 1 2 1 X



**MADE IN GERMANY** 

### Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG  
 Elso-Klöver-Str. 6  
 D-21337 Lüneburg  
 uvex-safety.de