



Silver Cut-off Wheels

Product Data Sheet

Date 02_2020
Supersedes: -

Product Name	3M Silver Cut-off Wheels
Product Description	3M Silver Cut-off wheels are reinforced resin-bonded wheels containing 3M-Proprietary Ceramic Precision Shaped Grain (PSG). 3M Silver Cut-off wheels are designed for cutting mild steel, stainless steel, and nickel alloys.
Mineral	A blend of 3M-Proprietary Ceramic Precision Shaped Grain (PSG) and crushed aluminum oxide
Construction	Resin bonded wheels with a construction for added safety and durability; INOX formulation (Fe < 0.1%, S < 0.1%, and Cl < 0.1%) for stainless steel applications
Available Forms/ Dimensions	Type 41 and Type 42 75mm, 105mm, 115mm, 125mm, 150mm, 180mm and 230mm with thickness from 0,9mm to 3mm
Identification	All relevant product identification information can be found on the product label or on the box in which the product was received or on the with the product supplied Safety Instruction Leaflet.
Recommended (Ideal) Storage Conditions	Store under "first-in - first-out" base and at recommended conditions (16-26°C/ 35-50% rH). Temperature and humidity beside these conditions should be avoided.
Safety	<p>Please refer to all local safety and industrial standards.</p> <p>Always use appropriate PPE and follow safety precautions as instructed in the associated Product Safety Insert. Product Safety Inserts are included with shipped product and are also available on-line through 3M.com</p> <p><u>This product should be used on guarded tools.</u></p>

For Additional Information	To request additional product information or to arrange for sales assistance, call your local 3M Application Engineering.
-----------------------------------	---

Important Notice	<p>All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law</p>
<p>Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations</p>	

For Additional Information

<p>3M UK Limited 3M Abrasive Systems Division 3M Centre Cain Road Bracknell RG12 8HT Tel: 08705 360036 abrasives.uk@mmm.com 3M.co.uk/metalworking</p>	<p>3M Ireland Limited 3M Abrasive Systems Division The Iveagh Building The Park Carrickmines Dublin 18 Ireland Tel: 1 800 320 500</p>	<p>3M Denmark a/s 3M Abrasive Systems Division Afd. Industri Hannemanns Allé 53 2300 København S Telefon 43 48 01 00 www.3M.dk</p>
<p>3M Finland Suomen 3M oy 3M Abrasive Systems Division Keilaranta 6 PL 600 02151 Espoo Puh: 09 525 21 www.3M.fi</p>	<p>3M Svenska AB Herrjarva torg 4 S170 67 Solna SWEDEN Telefon 08-92 21 00 E-post kundservice@mmm.com www.3M.se</p>	<p>3M Norge AS 3M Abrasive Systems Division Avd. Industri Postboks 100 2026 Skjetten Tel: 0 63 84 www.3M.no</p>
<p>3M Latvija 3M Abrasive Systems Division K. Ulmaņa gatve 5 Rīga, LV-1004 Telefons +371 67 066 120 www.3M.lv</p>	<p>3M Eesti OÜ 3M Abrasive Systems Division Pärnu mnt 158 11317 Tallinn Eesti Telefon +372 611 5900 www.3M.ee</p>	<p>3M Lietuva, 3M Abrasive Systems Division UAB A. Goštauto g. 40A LT-03163, Vilnius Lietuva Tel. +370 5 2160 119 www.3M.lt</p>

3M is a trademark of the 3M Company.