

Product data sheet for uvex protector NK4025B



The uvex protector family of safety gloves can easily overcome even the most complex challenges: the multi-layered structure of the material provides reliable cut protection and reliably guards the wearer against chemical and mechanical hazards.

Characteristics

- Ergonomic fit
- Good grip, even in wet work environments
- Long service life

Material number	60536
Sizes	9 - 10
Standard	EN 420:2003 + A1:2009, EN 388:2016, EN ISO 374-1:2016
Test chemicals	n-Heptane (J), Sodium hydroxide 40% (K), Acetic acid 99% (N), Ammonia water 25% (O), Hydrogen peroxide 30% (P), Formaldehyde 37% (T)
Performance class in accordance with EN 388	4 X 4 4 C
Outer material	Cotton interlock, High-performance polyethylene (HPE), Fibreglass, polyamide (PA)
Coating	Nitrile rubber (NBR)
Coating surface area	Fully coated
Type	With gauntlet
Colour	Blue

EN ISO 374-1:2016 / Type A



J K N O P T

EN 388:2016



4 X 4 4 C



MADE IN GERMANY 

Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG
 Elso-Klöver-Str. 6
 D-21337 Lüneburg
 uvex-safety.de