

## Product data sheet for uvex u-chem 3100



The uvex u-chem 3100 is a full chemical protection glove certified to EN ISO 374-1:2016/Type A (A J K L O T). This model also offers good mechanical protection and is therefore ideal for use in a wide range of applications.

### Characteristics

- Good grip, even in wet work environments
- Good fit
- Good mechanical abrasion resistance

<b>Material number</b>	60968
<b>Sizes</b>	8 - 11
<b>Standard</b>	EN 420:2003 + A1:2009, EN 388:2016, EN ISO 374-1:2016, EN ISO 374-5:2016
<b>Test chemicals</b>	Methanol (A), n-Heptane (J), Sodium hydroxide 40% (K), Sulphuric acid 96% (L), Nitric acid 65% (M), Ammonia water 25% (O)
<b>Performance class in accordance with EN 388</b>	4 1 2 1 X
<b>Outer material</b>	Cotton interlock
<b>Coating</b>	Nitrile rubber (NBR), Grip finish
<b>Coating surface area</b>	Fully coated
<b>Type</b>	With gauntlet
<b>Colour</b>	Black

EN ISO 374-1:2016 / Type A



A J K L M O

EN ISO 374-5:2016



EN 388:2016



4 1 2 1 X

### Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG  
 Elso-Klöver-Str. 6  
 D-21337 Lüneburg  
 uvex-safety.de