


**Product Datasheet model uvex pheos s 9192 283****UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth****Product  
characteristics**

- modern safety spectacles with a fashionable design and duo-spherical lens technology
- small version
- metal-free
- additional eyebrow protection with Eye Plus Protection: a bevelled edge in upper area
- soft, non-slip ear pieces (uvex duo Component technology) prevent pressure points
- very large field of vision
- can be easily combined with other PPE
- suitable for the uvex helmet IES (Integrated Eyewear System)

<b>Technical details</b>	
<b>Frame</b>	<b>Front piece/Temple</b>
Material	POM/TPE
Features	excellent ventilation
Colour	black-grey
	<b>Marking</b>
Manufacturer's ID code	W
Applicable EN norm	166
Low-energy impact	F (45 m/s)
Resistance to high speed particles at extremes of temp.	T
Conformity symbol	CE
<b>Lens</b>	
Material	PC
Thickness	2,1 mm
Coating	supravison extreme
Colour	grey
UV-Schutz	UV 400

	<b>Marking</b>
Filter	5-2,5 (DIN EN 172)
Manufacturer's ID code	W 1
Optical class	F (45 m/s)
Low-energy impact Resistance to high speed particles at extremes of temp.	T
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	
<b>Miscellaneous</b>	
Weight	30 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 172
PPE Category	Category II