


Product Datasheet model ultravision 9301 815

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics	<ul style="list-style-type: none">• Classic goggle with unrestricted field of vision• Can be worn over prescription spectacles• Lenses can be changed• High mechanical strength of the polycarbonate lens (B: 120 m/s)• innovative indirect ventilation system helps maintain a comfortable climate around the eyes
Technical details	
Frame	Front piece
Material	PVC
Features	top ventilation closed
Colour	transparent light grey

Material	Headband synthetic headband
Features	adjustable
Colour	anthracite, lime
Mounting	PC headband clip
Manufacturer's ID code	Marking W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles) 9 (molten material and hot solids)
Impact resistance	B (120 m/s)
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,2 mm
Coating	uvex supravision excellence
Colour	clear
UV protection	UV 400
Filter	Marking 2C-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Low-energy impact	B (120 m/s)
Field of use	9 (molten material and hot solids)
Surface resistance to fine particles	K
Antifog	N
Conformity symbol	CE
Factory symbol	

Miscellaneous

Weight	130 g
Packing	90 pieces in one carton
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II