

Series 7400 Kraffform torque screwdrivers with a customised factory pre-set measurement value, handle size 105 mm, 7460 x 0.3-1.2 Nm

Series 7400 Kraffform Torque Screwdrivers, adjustable to customer requirements within the specified measurement range



EAN:	4013288188144	Size:	155x37x37 mm
Part number:	05074715010	Weight:	180 g
Article number:	7400 customized pre-set, 105 mm	Country of origin:	CZ
		Customs tariff number:	82054000

- Customized pre-set torque screwdriver with Rapidaptor quick-release chuck
- Only adjustable with an extra tool
- Suitable for bits with 1/4" hex head drive
- Rapidaptor technology for rapid bit change
- Distinct signal when pre-set value is reached
- Multi-component Kraffform handle for high working speeds

Wera torque screwdriver. With a customised factory pre-set torque value. For all applications, where the same constant torque and repeat accuracy are required. The torque can be changed with an extra tool within the measuring range (re-calibration kit can be ordered with the code number 05137001001). Afterwards you can check the set value using an off-the-shelf torque tester. Unlimited loosening torque for slackening stuck screws. Rapidaptor quick-release technology for rapid bit changes. Suitable for bits with a 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173). Multi-component Kraffform handle with hard and soft zones for high working speeds, whilst being easy on the hand.

Please note: 1 Ncm = 0.01 Nm.



Web link

https://products.wera.de/en/torque_tools_series_7400_kraffform_torque_screwdrivers_adjustable_to_customer_requirements_within_the_specified_measurement_range_7400


Wera - 7400 customized pre-set, 105 mm
05074715010 - 4013288188144

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Series 7400 Krafftform torque screwdrivers with a customised factory pre-set measurement value, handle size 105 mm, 7460 x 0.3-1.2 Nm
 Series 7400 Krafftform Torque Screwdrivers, adjustable to customer requirements within the specified measurement range



Customised pre-setting



Wera torque screwdriver. With a customised factory pre-set torque value. For all applications, where the same constant torque and repeat accuracy are required.

Unlimited torque



Unlimited torque for loosening seized screws.

Versatile



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

Chuck-all



The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out








Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Single-hand function



Every function of the Rapidaptor quick-release chuck, such as inserting or releasing bits, can be carried out with one hand. This is faster, more economical and more ergonomic. There are no unnecessary manoeuvres.

Further versions in this product family:

	art. no.	 inch	 Nm	 mm	 mm	 inch
05074715010¹⁾	7460	1/4"	0.3-1.2	105	155	6"
05074716010 ¹⁾	7461	1/4"	1.2-3.0	105	155	6"

¹⁾ The desired settings can be made in the following units: Nm, kgf. m, lbf. ft., ozf. in., dN. m, kgf. cm, lbf. in, in. oz, cN. m, gf. m, ft. lb, gf. cm, in. lb.

Web link

https://products.wera.de/en/torque_tools_series_7400_krafftform_torque_screwdrivers_adjustable_to_customer_requirements_within_the_specified_measurement_range_7400

Wera - 7400 customized pre-set, 105 mm
 05074715010 - 4013288188144

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de