

## uvex Eye Protection System

### High Performance Eyewear

#### uvex i-vo

- Approved to AS/NZS 1337.1 - medium impact protection
- 100% UV protection
- Lens coating available in:
  - uvex supravision excellence lens coating (ideal for strenuous activity in dusty and abrasive environments)
  - uvex supravision sapphire (ideal in highly abrasive dirty and dusty work environments)
  - uvex supravision THS (ideal when constantly moving between areas of different temperatures and humidities)
- Outstanding peripheral vision
- 5 point lens inclination for individual fit
- soft, ergonomically designed nose bridge for comfort
- Patented Duo Component Technology
- 4 point length adjustable side arms with quatreflex temple ends



uvex Point of Difference	Benefits
uvex supravision excellence	Extremely scratch resistant on the outside and permanent anti-fog on the inside of the lens
uvex supravision sapphire	Extremely scratch resistant on both sides of the lens with nano-technology for easy clean
uvex supravision THS	Superior anti-fog on both sides of the lens
Sophisticated 5 point lens inclination system	Fits a wider range of facial features
Frame design (front)	Offers extra ventilations for high humidity conditions

#### Target Applications (but not limited to):

- Roadworks
- Construction industry
- Mining industry
- Transport industry

#### Packaging:

- 5 pairs per box
- 100 pairs per carton

#### Barcodes:

- 9160-001 - 9321123008607
- 9160-004 - 9321123008621
- 9160-120 - 9321123008591
- 9160-301 - 9321123008614

#### Part Numbers:

- 9160-001 - clear 80%+ VLT cat 0, uvex sv sapphire lens, blue/grey frame
- 9160-004 - grey 20% VLT cat 2, uvex sv sapphire lens blue/grey frame
- 9160-120 - clear 80%+ VLT cat 0, uvex sv excellence lens, blue/grey with headband
- 9160-301 - clear 80%+ VLT cat 0, uvex sv THS lens, blue grey frame

#### Cleaning accessories:

- 1009 - 'uvex clear' lens cleaning fluid, 500ml bottle
- 1008 - uvex replacement lens cleaning tissues
- 1005 - 'uvex clear' lens cleaning towelettes