

# TECHNICAL DATA SHEET

**BRICE Air XXTM black Low ESD S1P No. 710541**


**Sz. 36 - 48**



## LABELLING ACCORDING TO STANDARD

Standard for safety footwear EN ISO 20345 S1P	Basic requirement for S1P: <b>A</b> Antistatic shoe - <b>E</b> Energy absorption in the heel - <b>FO</b> Fuel resistance - <b>P</b> Penetration resistance - Closed heel area
Additional requirements	<b>SRC</b> Slip resistance: Slip resistant on floors of ceramic tiles with a sodium lauryl sulfate (SLS) solution and on steel floors with glycerol. When it comes to slip resistance as defined by EN ISO 20345, SRC signifies the best possible rating a safety shoe can reach.


## FORM

Safety shoe 	Form A - in size 42, the upper height must not exceed 11.2 cm.
----------------------------------------------------------------------------------------------------	----------------------------------------------------------------


## AREAS OF APPLICATION

Areas of application	<p>Dry work areas Industry, storage, transport, assembly etc. Areas where there is a risk of penetration from pointed and sharp objects (S1P)</p> <p>Areas where there is a risk of electrostatic discharge (ESDS/ESD)</p> <p>Workplaces on hard Undergrounds: The revolutionary Infinergy® sole core cushions impacts and provides for a rebound effect when the compressive impulse subsides - for more energy in every step.</p>
----------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

## FEATURES

ESD equipment	Thanks to its excellent discharge capability, the shoe is suitable for work in ESD sensitive or electrostatically protected areas (EPA). The shoes comply to the standard 61340-5-1.	
Sizes (unisex model)	<ul style="list-style-type: none"> <li>Expanded size range: available in sizes 36 - 48</li> </ul>	

## FEATURES

Certification in accordance with DGUV rule 112-191	<ul style="list-style-type: none"><li>• Certified for orthopaedic inserts</li></ul>	
Padded upper edge	<ul style="list-style-type: none"><li>• Excellent wearing comfort: the padded upper edge protects the Achilles tendon.</li></ul>	
No metal or leather	<ul style="list-style-type: none"><li>• Low weight</li><li>• Suitable for work areas sensitive to metal</li><li>• Does not trigger metal detectors</li><li>• Use around induction loops is possible</li><li>• Suitable for persons allergic to leather</li></ul>	


## UPPER MATERIAL

Microfibre	<ul style="list-style-type: none"><li>• Synthetic material</li><li>• Particularly soft</li><li>• Retains its shape</li><li>• Tear-resistant</li><li>• Quick drying</li><li>• Abrasion-resistant and light</li></ul>	
------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--

## LINING

Breathable fabric lining	<ul style="list-style-type: none"><li>• Climate-regulating</li><li>• Good ventilation</li><li>• Skin-friendly</li><li>• High absorption and emission of moisture</li></ul>	
Heel pocket lining	<ul style="list-style-type: none"><li>• The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort.</li></ul>	

## TOE PROTECTION CAP

Composite toe cap 	<ul style="list-style-type: none"><li>• Protection against impacts of min. 200 joules and pressure loading of min. 15 kN</li><li>• Permanent edge coverage for cushioning</li><li>• Ergonomically shaped</li><li>• Comfortable toe room</li><li>• Good coverage of the little toe area</li><li>• Low weight - weighs less than conventional steel caps</li><li>• 100% metal-free</li><li>• 100% anti-magnetic</li></ul>	
----------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--

## INLAY SOLE

## PENETRATION RESISTANCE

Metal-free penetration protection

The textile midsole complies with the penetration safety standard EN 12568 and furthermore fulfils the additional requirements for penetration protection in accordance with EN ISO 20344 / 20345. The light and flexible material enables an increased elasticity of the shoe, which can particularly be recognized when working on uneven grounds or on your knees.

The textile variant offers 100 % foot coverage compared to steel midsoles (foot coverage 85 % due to limits in the shoe manufacturing process). Being 100 % metal-free and antimagnetic, this equipment is used as penetration protection in safety shoes.

## OUTSOLE

WELLMAXX TRAINERS  
MONO mono-density sole  
with profile



- Excellent slip resistance
- Antistatic

Outsole: PU (polyurethane)

- Colour: black
- Profile depth: 3.5 mm
- Abrasion-resistant
- Heat-resistant to approx. 130°C
- Flexible at cold temperatures to approx. -20°C
- Notch-resistant
- Oil and fuel resistant
  
- The core made of Infinergy® provides a very good cushioning with rebound effect