

Product data sheet for uvex rubiflex NB80SZ



For these chemical protection gloves, a thicker cotton interlock lining is used. This makes the uvex rubiflex S suitable for many applications in which protection against chemicals and increased mechanical protection (for example against heat) is required. The special 60 or 80 cm version is also available with elasticated gauntlet end.

Characteristics

- Ergonomic fit
- Good grip
- Very good tactile feel

Material number	60191
Sizes	9 - 11
Standard	EN 420:2003 + A1:2009, EN 388:2016, EN ISO 374-1:2016
Test chemicals	Sodium hydroxide 40% (K), Ammonia water 25% (O), Formaldehyde 37% (T)

EN ISO 374-1:2016 / Type B



EN 388:2016



MADE IN GERMANY

Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG
 Elso-Klöver-Str. 6
 D-21337 Lüneburg
 uvex-safety.de

Performance class in accordance with EN 388 2 1 2 1 X

Performance class in accordance with EN 407 X 1 X X X X

Outer material	Cotton interlock
Coating	Nitrile rubber (NBR)
Coating surface area	Fully coated
Coating thickness	0.50 mm
Type	With gauntlet and elasticated band
Colour	Green
Glove length	80 cm