

Product data sheet for uvex rubiflex S XG27B



The lightweight uvex rubiflex S XG chemical protection glove with innovative Xtra Grip coating. It combines protection and grip with outstanding comfort and flexibility. As well as being comfortable to wear, stockinette chemical protection gloves also offer good protection against a wide variety of chemical and mechanical hazards.

Characteristics

- Ergonomic fit
- Good grip, even in wet work environments
- Good mechanical abrasion resistance
- Very good tactile feel

Material number	60560
Sizes	7 - 11
Standard	EN 420:2003 + A1:2009, EN 388:2016, EN ISO 374-1:2016

Test chemicals	n-Heptane (J), Sodium hydroxide 40% (K), Acetic acid 99% (N), Ammonia water 25% (O), Hydrogen peroxide 30% (P), Formaldehyde 37% (T)
-----------------------	--

Performance class in accordance with EN 388	3 1 2 1 X
--	-----------

Performance class in accordance with EN 407	X 1 X X X X
--	-------------

Outer material	Cotton interlock
Coating	Nitrile rubber (NBR), Xtra Grip
Coating surface area	Fully coated
Coating thickness	0.40 mm
Type	With gauntlet
Colour	Blue, Black

EN ISO 374-1:2016 / Type A



J K N O P T

EN 388:2016



3 1 2 1 X



MADE IN GERMANY

Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG
 Elso-Klöver-Str. 6
 D-21337 Lüneburg
 uvex-safety.de