

3M Science.
Applied to Life.™

3M™ Riveters Tape 695

Last Revision Date: June, 2017

Product Description

3M™ Riveters Tape 695 is a zone-coated polyethylene film tape with a tack-free center “window” for use in holding aircraft rivets in place prior to and during riveting.




Product Features

- Yellow translucent tack-free center “window” helps ensure easy visibility of rivets.
- Does not contribute to aircraft skin damage like some polyester film backings.
- Does not adhere to rivets.
- Good immediate adhesion to aluminum.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Property	Values	Additional Information
Backing	Polyethylene film	
Adhesive Type	Acrylic, strip coated along edges of tape only	
Color	White adhesive, yellow translucent film in uncoated center section	
Backing Thickness (mm)	0.051 mm	View 
Test Method: ASTM D3652		
Total Tape Thickness (mil)	3 mil	View 
Test Method: ASTM D3652		
Total Tape Thickness (mm)	0.076 mm	View 
Test Method: ASTM D3652		

Backing Thickness	2 mil	View 
-------------------	-------	--


Test Method: ASTM D3652

Typical Performance Characteristics

Property	Values	Additional Information
----------	--------	------------------------

Tensile Strength	14 N/cm	View 
------------------	---------	--

Test Method: ASTM D3759

180° Peel Adhesion	1.6 N/cm	View 
--------------------	----------	--


Test Method: ASTM D3330

Notes: 12 in/min (300 mm/min)

180° Peel Adhesion	15 oz/in	View 
--------------------	----------	--

Test Method: ASTM D3330

Notes: 12 in/min (300 mm/min)

Tensile Strength	128 oz/in	View 
------------------	-----------	--

Test Method: ASTM D3759

Long Term Temperature Resistance	49 °C	
----------------------------------	-------	--

Minimum Long Term Temperature Resistance	-29 °C	
--	--------	--

Long Term Temperature Resistance	120 °F	
----------------------------------	--------	--

Minimum Long Term Temperature Resistance	-20 °F	
--	--------	--

Available Sizes

Property	Values	Additional Information
----------	--------	------------------------

Standard Roll Length	32.9 m	
----------------------	--------	--

Standard Roll Length	36 yd	
----------------------	-------	--

Width	1 in. (25 mm) and 2 in. (50 mm) with 1/4 in. (6.4 mm) adhesive strip on each edge
-------	---

Storage and Shelf Life

Store in a clean, dry environment at 60° to 80°F (16° to 27°C) and 40 to 50% relative humidity. To obtain best performance, use this product within 18 months from date of manufacture.

Bottom Matter

3M
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550

References

Property	Values
3m.com Product Page	https://www.3m.com/3M/en_US/p/d/b40070661/
Safety Data Sheet SDS	https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&msdsLocale=en_US&co=ptn&q=695

Family Group

Link Tags:

• [695](#)

Products	Backing	Adhesive Type	Color	Backing Thickness (mm)	Total Tape Thickness (mm)	Tensile Strength	Long Term Temperature Resistance	Minimum Long Term Temperature Resistance
695	Polyethylene film	Acrylic, strip coated along edges of tape only	White adhesive, yellow translucent film in uncoated center section	0.051 mm	0.076 mm	14 N/cm	120 °F	-29 °C

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to

property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.