

**Product Datasheet model uvex pheos s 9192 282**

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,  
D-90766 Fürth**

**Product  
characteristics**

- modern safety spectacles with a fashionable design and duo-spherical lens technology
- small version
- metal-free
- additional eyebrow protection with Eye Plus Protection: a bevelled edge in upper area
- soft, non-slip ear pieces (uvex duo Component technology) prevent pressure points
- very large field of vision
- can be easily combined with other PPE
- suitable for the uvex helmet IES (Integrated Eyewear System)

**Technical details****Frame**

Material  
Features  
Colour

**Front piece/Temple**

POM/TPE  
excellent ventilation  
black-grey

Manufacturer's ID  
code  
Applicable EN norm  
Low-energy impact  
Resistance to high  
speed particles at  
extremes of temp.  
Conformity symbol

**Marking**

W  
  
166  
F (45 m/s)  
T  
  
CE

**Lens**

Material  
Thickness  
Coating  
Colour  
UV protection

PC  
2,1 mm  
supravision extreme  
clear  
UV 400

Filter	<b>Marking</b>
Manufacturer's ID code	2C-1,2 (DIN EN 170)
Optical class	W
Low-energy impact	1
Resistance to high speed particles at extremes of temp.	F (45 m/s)
Surface resistance to fine particles	T
Antifog	K
Conformity symbol	N
	CE
<b>Miscellaneous</b>	
Weight	30 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II