

uvex

SAFETY EYEWEAR


24.01.2020

Product Datasheet model pheos cx2 9198 885



**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics	<ul style="list-style-type: none">• x-branded safety spectacles with a modern, sporty design• comfortable protection with the x-tended eyeshield• x-twist side arm technology delivers non-slip fit for optimum protection• duo-spherical lens delivers excellent field of vision• large field of vision• innovative uvex duo component technology for maximum wearer comfort• can easily be combined with other PPE• uvex supravision coating technology
Technical details	
Frame	Front piece/Temple
Material	POM/TPE
Colour	blue, grey

Manufacturer's ID code	Marking W
Applicable EN norm	166
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Conformity symbol	CE
Lens	
Material	PC
Thickness	2,2 mm
Coating	AF on the inside
Colour	silver mirror grey
UV protection	UV 400
Filter	Marking 5-3,1 (DIN EN 172)
Manufacturer's ID code	W
Optical class	1
Impact resistance	F (45 m/s)
Resistance to high speed particles at extremes of temperat.	T
Antifog	N
Conformity symbol	CE
Factory symbol	
Miscellaneous	
Weight	28 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 172
PPE Category	Category II