

TECHNICAL DATA SHEET

MARAIS black Low ESD O1 No. 972080


Sz. 36 - 48



LABELLING ACCORDING TO STANDARD

| | |
|--|---|
| Standard for occupational shoes EN ISO 20347 O1 | Basic requirement for O1: A Antistatic shoe - E Energy absorption in the heel - Closed heel area |
| Additional requirements | SRC Slip resistance: Slip resistant on floors of ceramic tiles with a sodium lauryl sulfate (SLS) solution and on steel floors with glycerol. When it comes to slip resistance as defined by EN ISO 20345, SRC signifies the best possible rating a safety shoe can reach. HRO HEAT RESISTANT OUTSOLE Heat resistance against contact heat, also during short-term high temperatures FO FUEL RESISTANCE |


FORM

| | |
|---|--|
| Occupational work shoe  | Form A - in size 42, the upper height must not exceed 11.2 cm. |
|---|--|


AREAS OF APPLICATION

| | |
|----------------------|--|
| Areas of application | Dry work areas Areas where there is no risk of falling heavy objects Areas where there is a risk of electrostatic discharge (ESDS/ESD) |
|----------------------|--|

FEATURES

| | |
|----------------------|--|
| ESD equipment | Thanks to its excellent discharge capability, the shoe is suitable for work in ESD sensitive or electrostatically protected areas (EPA). The shoes comply to the standard 61340-5-1.  |
| Sizes (unisex model) | <ul style="list-style-type: none"> Expanded size range: available in sizes 36 - 48 |

FEATURES

| | |
|--|--|
| Certification in accordance with DGUV rule 112-191 | <ul style="list-style-type: none"> • Certified for orthopaedic inserts  |
| Low weight | <ul style="list-style-type: none"> • Use of especially light textile materials • Comfortable |
| Low weight sole | <ul style="list-style-type: none"> • Comfortable |
| Padded upper edge | <ul style="list-style-type: none"> • Excellent wearing comfort: the padded upper edge protects the Achilles tendon. |
| Padded tongue | <ul style="list-style-type: none"> • Excellent wearing comfort: The tongue prevents pressure marks. |
| Leather-free equipment | <ul style="list-style-type: none"> • Suitable for persons allergic to leather |
| Winner Plus X Award | <p>The independent jury for the Plus X Award, the Innovation Prize for Technology, Sport, and Lifestyle, grants a total of seven seals of approval to brands that offer products with a competitive edge in terms of quality and innovation. ELTEN has always seen itself as an innovative business at the cutting edge of technology.</p>  |


UPPER MATERIAL

| | |
|---------------|--|
| Mesh material | <ul style="list-style-type: none"> • Areas of application S1 • Synthetic material • Retains its shape • Tear-resistant • Quick drying • Abrasion-resistant and light |
|---------------|--|

LINING

| | |
|--------------------------|---|
| Breathable fabric lining | <ul style="list-style-type: none"> • Climate-regulating • Good ventilation • Skin-friendly • High absorption and emission of moisture |
| Heel pocket lining | <ul style="list-style-type: none"> • The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort. |

INLAY SOLE

| | |
|---|---|
| <p>Full-length inlay sole ESD PRO</p>  | <ul style="list-style-type: none"> • ESD EQUIPMENT: Protection against electrostatic discharge (ESD). The full-length, exchangeable inlay sole is conductive and designed for the use in ESD safety footwear according to the standards DIN EN ISO 20345 and DIN EN 61340-5-1. • The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes. • The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate. • The extreme softness of the PU foam absorbs shocks on impact and increases walking comfort. • Improvement of the shoe climate thanks to the PU foam's open cell structure. So the foot is always kept comfortably dry. |
|---|---|

INSOLE

ESD soft-fleece insole

ESD equipment: Protection against electrostatic discharge (ESD), and without using additional means fulfilling a bridge function to the outsole.

- Approximately 50 % lighter than comparable soles made of natural materials
- Flexible and shape-retaining
- Good air permeability
- Excellent wear resistance
- High moisture absorption
- Quick drying (virtually overnight)

OUTSOLE

TRANSFOAMERS double-density sole with profile



- Antistatic
- Excellent slip resistance
- ultralight, very flexible sole

Outsole: Rubber

- Colour: black
- Profile depth: 2.5 mm
- Particularly abrasion-resistant
- Heat-resistant to approx. 200°C, for short periods to 300°C
- Flexible at cold temperatures to approx. -20°C
- Oil and fuel resistant
- Excellent damping qualities
- Low material density, thereby lower weight

Midsole: EVA (Ethylene-Vynil-Acetat)/TPU (thermoplastic polyurethane)

- Innovative midsole foam made of EVA and TPU, among other materials, for lightness and durability
- Excellent damping qualities
- Low material density, thereby lower weight