



## TP 6600 (without float switch)

- For pumping empty, pumping dry and circulating clear water from containers, tanks, tanks or flooded cellars
- For garden irrigation from water reservoirs
- Overload protection: protects the motor from overheating
- Robust housing made of impact-proof plastic
- Ergonomic handle for comfortable transport

Order no.	0250660000
EAN code	4003665502236
Rated input power	250 W
Maximum delivery rate	6600 l/h / 1744 gal/h
Maximum delivery height	6 m / 20 ft
Maximum pressure	0.6 bar / 8.7 psi
Maximum immersion depth	5 m / 16.4 ft
Discharge port	1 1/4" female thread
Pump housing	Plastic
Protection type IP	IP X8
Maximum particle size up to	3 mm / 1/8 "
Number of impellers	1
Dimensions	250 x 195 x 270 mm // 9 27/32 x 7 11/16 x 10 5/8 "
Weight	4.3 kg / 9.5 lbs
Cable length	10 m / 33 ft

### Scope of delivery

Angle connection piece with multi-adapter