



TPF 6600 SN

- For pumping empty, pumping dry and circulating clear water from containers, tanks, tanks or flooded cellars
- For garden irrigation from water reservoirs
- Overload protection: protects the motor from overheating
- Low-intake level up to a residual water level of 2-3 mm
- Adjustable float switch for automatic mode
- Durable housing made of non-corrosive stainless steel
- Ergonomic handle for comfortable transport

Order no.	0250660006
EAN code	4003665502243
Rated input power	450 W
Maximum delivery rate	6600 l/h / 1744 gal/h
Maximum delivery height	6 m / 20 ft
Maximum pressure	0.6 bar / 8.7 psi
Maximum immersion depth	5 m / 16.4 ft
Discharge port	1 1/4" female thread
Pump housing	Stainless steel
Protection type IP	IP X8
Maximum particle size up to	3 mm / 1/8 "
Number of impellers	1
Dimensions	257 x 195 x 270 mm // 10 1/8 x 7 11/16 x 10 5/8 "
Weight	4.6 kg / 10.1 lbs
Cable length	10 m / 33 ft

Scope of delivery

Angle connection piece with multi-adapter, Float switch