



PS 18000 SN

- For pumping empty, pumping dry and circulating fresh water or dirty water from containers, tanks or flooded cellars
- For garden irrigation from water reservoirs
- Double seal system for protection of the pump if the water is particularly dense or contains large particles
- Overload protection: protects the motor from overheating
- Adjustable float switch for automatic mode
- Durable housing made of non-corrosive stainless steel
- Ergonomic handle for comfortable transport

Order no.	025180000
EAN code	4003665502311
Rated input power	1100 W
Maximum delivery rate	19000 l/h / 5019 gal/h
Maximum delivery height	11 m / 36 ft
Maximum pressure	1.1 bar / 16 psi
Maximum immersion depth	7 m / 23 ft
Discharge port	1 1/2" female thread
Pump housing	Stainless steel
Protection type IP	IP X8
Maximum particle size up to	35 mm / 1 3/8 "
Number of impellers	1
Dimensions	265 x 200 x 360 mm // 10 7/16 x 7 7/8 x 14 3/16 "
Weight	7.9 kg / 17.4 lbs
Cable length	10 m / 33 ft

Scope of delivery

Angle connection piece with multi-adapter, Float switch