



LSV 5-225

- For convenient sanding of primed surfaces on walls or ceilings
- Optimum balance when working, as the centre of gravity of the machine is not at the sanding head
- M-Clean technology: Effective extraction through the machine housing for maximum flexibility of the sanding head
- Ideal adaptation of the flexible sanding head to the surface for good work results
- Optimum extraction results thanks to spring-mounted brush rim that adapts to the surface.
- Vario-Constamatic (VC)-Full wave electronics for working at customised speeds to suit the application materials, and speeds that remain almost constant even under load
- Low weight reduces fatigue when working continuously
- Ergonomically shaped aluminium handle bar and T-handle for comfortable use in different positions
- Simple, quick and tool-free exchangeable shaft can be adjusted directly on site if needed
- Putting the machine down without kinking the hose and cable
- With extensive range of grinding media for every application
- Extraction possibility by means of connecting an all-purpose vacuum cleaner

| Order no. | 600103000 |
|------------------------------|--------------------|
| EAN code | 4007430282668 |
| Sanding disc diameter | 225 mm / 8 7/8 " |
| No-load speed | 1000 - 1650 rpm |
| Rated input power | 500 W |
| Output power | 270 W |
| Adjustable machine length | 1.6 m // 61 7/32 " |
| Weight (without power cable) | 3.8 kg / 8.38 lbs |
| Cable length | 4 m / 157 1/2 " |

Scope of delivery

Sanding pad (very soft), Hook and loop sanding sheets with multi-perforation (1 each of P80, P100, P120, P150), Flexible shaft (as replacement), Coupling bush, Hexagonal wrench, Tool bag