



MH 5

- Metabo VibraTech (MVT): integrated damping system to reduce vibrations in order to protect the user's health
- Optimum heat dissipation and low weight thanks to die cast magnesium gear housing
- Lockable switch for comfortable chiselling in continuous operation
- The adjustable front handle can be rotated 360° and the angle adjusted for an optimum working position

Order no.	600147500
EAN code	4061792199200
Max. single blow energy (EP-TA)	7.1 J
Maximum impact rate	3000 bpm
Rated input power	1100 W
Bit retainer	SDS-max
Weight (without power cable)	5.6 kg
Cable length	6 m / 19.685 ft

Scope of delivery

Front handle, Lubricant for tool shank end, Duster, Plastic carry case