



SPA 1702 W

- Raw air extraction device for (semi) stationary wood processing machines (observe country-specific regulations!)
- Significantly reduces dust content
- Filter material of dust class L
- Quick change of the application location by means of wheeled unit and simple connection
- Stable stand with supported chip collection bag
- Comprehensive range of accessories: automatic switch-on devices, filter cartridges, hoses and adapters

Order no.	0130170100
EAN code	4003665398358
Dimensions	882 x 562 x 1671 mm // 2.9 x 1.9 x 5.5 ft
Maximum vacuum	1730 Pa / 0.2 psi
Maximum volume flow	1010 m ³ /h / 266813 gal/h
Filter surface	1.1 m ² / 1705 sq.inch
Hose connection Ø	100 mm / 4 "
Chip bag capacity	90 l / 24 gal
Mains voltage	220 - 240 V
Rated input power	0.75 kW
Weight	24 kg / 53 lbs

Scope of delivery

Suction hose 100 x 2500 mm, Filter bag made of needle felt, Chip Collection Bag