



B 32/3

- Powerful three-speed drill with extra high torque for working in a drill stand
- Robust mechanical gearbox with oil bath lubrication
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Vario (V)-Electronics for working at customised speeds to suit various application materials
- Safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- For easy drilling of larger diameters and driving in of very long screws

Order no.	600323000
EAN code	4007430172204
Rated input power	1800 W
Output power	1200 W
Drill Ø steel	32 mm // 1 1/4 "
Drill-Ø soft wood	70 mm // 2 3/4 "
No-load speed	0 - 170 / 0 - 320 / 0 - 470 rpm
Speed at rated load	110 / 190 / 280 rpm
Gears	3
Maximum torque	190 / 120 / 90 Nm // 1682 / 1062 / 797 in-lbs
Collar diameter	65 mm / 2 9/16 "
Drill spindle with inside taper	MT 3
Weight (without power cable)	7.8 kg / 17.2 lbs
Cable length	5 m / 16 ft

Scope of delivery

Drift key