



TKHS 315 C - 2,0 WNB Set with 1x carbide saw blade (24 teeth) and 1x carbide saw blade (48 teeth 15°)

- Restart protection: prevents unintentional start-up after power supply interruption
- Universal table saw with basic equipment
- Ideal for sawing squared timber, boards, panels and wood-like materials in the workshop and at construction sites
- Quiet induction motor with motor brake and overload protection - maintenance-free and robust.
- Universal guide with magnetic guide for precise straight cuts and mitre cuts
- Freely height-adjustable saw blade
- Comfortable setting of the saw blade inclination from the front
- Sturdy, powder-coated sheet steel design and galvanised table-top
- Foldable table length extension
- Frame and motor pre-mounted

Order no.	0193152023
EAN code	4003665410821
Dimensions	1650 x 650 x 1000 mm // 5.5 x 2.2 x 3.3 ft
Max. support surface	800 x 550 mm // 31 1/2 x 21 5/8 "
Working height	850 mm // 33 1/2 "
Cutting height	0 - 85 mm // 0 - 3 5/16 "
Maximum cutting height	85 / 60 mm // 3 5/16 / 2 3/8 "
Maximum cutting width at rip fence	290 mm / 11 3/8 "
Maximum material width at mitre fence	220 mm / 8 5/8 "
No-load speed	2980 rpm
Cutting speed	50 m/s / 164 ft/s
Saw blade	315 x 30 mm // 12 3/8 x 1.181 "
Saw blade swivel range	0 - 45 °
Mains voltage	220 - 240 V
Rated input power	2000 W
Weight	62 kg / 137 lbs

Scope of delivery

Carbide saw blade with alternately bevel-ground tips (24 teeth), Carbide saw blade with alternately bevel-ground tips (48 teeth), Wheel set incl. handles, Universal guide, Table extension (550 x 800 mm), Chip and Dust Extraction Unit, Push stick