



PS 15000 S

- For pumping empty, pumping dry and circulating fresh water or dirty water from containers, tanks or flooded cellars
- For garden irrigation from water reservoirs
- Double seal system for protection of the pump if the water is particularly dense or contains large particles
- Overload protection: protects the motor from overheating
- Adjustable float switch for automatic mode
- Robust housing made of impact-proof plastic
- Ergonomic handle for comfortable transport

Order no.	025150000
EAN code	4003665502304
Rated input power	850 W
Maximum delivery rate	15000 l/h / 3963 gal/h
Maximum delivery height	9.5 m / 31 ft
Maximum pressure	0.95 bar / 13.8 psi
Maximum immersion depth	5 m / 16.4 ft
Discharge port	1 1/4" female thread
Pump housing	Plastic
Protection type IP	IP X8
Maximum particle size up to	30 mm / 1 3/16 "
Number of impellers	1
Dimensions	257 x 200 x 345 mm // 10 1/8 x 7 7/8 x 13 19/32 "
Weight	6.5 kg / 14.3 lbs
Cable length	10 m / 33 ft

Scope of delivery

Angle connection piece with multi-adapter, Float switch