



KHE 5-40

- Combination hammer with 2 functions: hammer drilling and chiselling
- Metabo VibraTech (MVT): integrated damping system to reduce vibrations in order to protect the user's health
- Easily accessible locking switch for chiselling in continuous mode
- Vario-Constamatic (VC)-Full wave electronics for working at customised speeds to suit the application materials, and speeds that remain almost constant even under load
- Thumbwheel for preselection of the speed and impact rate
- Electronic soft start for precise spot-drilling
- Optimum heat dissipation and low weight thanks to die cast magnesium gear housing
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- Restart protection: prevents unintentional start-up after power supply interruption
- Low-dust chiselling and drilling with external dust extraction ESA max (accessories)
- Wear Indication for Carbon Brush
- Service display, e.g. to indicate when the carbon brush needs to be replaced, and an LED indicating mains voltage
- Early warning system thanks to service LED for targeted planning of the carbon brush replacement 8 working hours before switching off

Order no.	600391500
EAN code	4061792199255
Max. single blow energy (EP-TA)	8.5 J
Maximum impact rate	3000 bpm
Rated input power	1100 W
Drill-Ø concrete with hammer drills	40 mm / 1 9/16 "
No-load speed	350 - 540 rpm
Speed at rated load	540 rpm
Bit retainer	SDS-max
Collar diameter	61 mm / 2.4 "
Weight (without power cable)	7.1 kg
Cable length	6 m / 19.7 ft

Scope of delivery

Side handle, Drilling depth guide, Lubricant for tool shank end, Duster, Plastic carry case