



MHE 5

- Metabo VibraTech (MVT): integrated damping system to reduce vibrations in order to protect the user's health
- Vario-Constamatic (VC)-Full wave electronics for working at impact rates to suit the application materials, and that remain almost constant even under load
- Thumbwheel for preselection of impact rate
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Optimum heat dissipation and low weight thanks to die cast magnesium gear housing
- Lockable switch for comfortable chiselling in continuous operation
- Service display, e.g. to indicate when the carbon brush needs to be replaced, and an LED indicating mains voltage
- Early warning system thanks to service LED for targeted planning of the carbon brush replacement 8 working hours before switching off
- The adjustable front handle can be rotated 360° and the angle adjusted for an optimum working position

Order no.	600148500
EAN code	4061792199231

Max. single blow energy (EP-TA)	7.1 J
Maximum impact rate	3000 bpm
Rated input power	1100 W
Bit retainer	SDS-max
Weight (without power cable)	5.7 kg
Cable length	6 m / 19.685 ft

Scope of delivery

Front handle, Lubricant for tool shank end, Duster, Plastic carry case